SIEMENS

## Data sheet for SIMOTICS S-1FK7

**MLFB-Ordering data** **1FK7100-2AF71-1BG2**



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

### Engineering data

| | |
|---|---|
| Rated speed (100 K) | 3000 rpm |
| Number of poles | 8 |
| Rated torque (100 K) | 12.0 Nm |
| Rated current | 8.0 A |
| Static torque (60 K) | 14.90 Nm |
| Static torque (100 K) | 18.00 Nm |
| Stall current (60 K) | 9.00 A |
| Stall current (100 K) | 11.10 A |
| Moment of inertia | 54.000 kgcm² |
| Efficiency | 92.0 % |

### Physical constants

| | |
|---|---|
| Torque constant | 1.62 Nm/A |
| Voltage constant at 20° C | 104.5 V/1000*min⁻¹ |
| Winding resistance at 20° C | 0.32 Ω |
| Rotating field inductance | 7.3 mH |
| Electrical time constant | 22.50 ms |
| Mechanical time constant | 2.00 ms |
| Thermal time constant | 55 min |
| Shaft torsional stiffness | 183000 Nm/rad |
| Net weight of the motor | 17.6 kg |

### Mechanical data

| | |
|---|---|
| Motor type | Permanent-magnet synchronous motor |
| Motor type | Compact |
| Shaft height | 100 |
| Cooling | Natural cooling |
| Radial runout tolerance | 0.050 mm |
| Concentricity tolerance | 0.10 mm |
| Axial runout tolerance | 0.10 mm |
| Vibration severity grade | Grade A |
| Connector size | 1 |
| Degree of protection | IP65 and DE flange IP67 |
| Design acc. to Code I | IM B5 (IM V1, IM V3) |
| Temperature monitoring | Pt1000 temperature sensor |
| Electrical connectors | Connectors for signals and power rotatable |
| Color of the housing | Standard (Anthracite RAL 7016) |
| Holding brake | without holding brake |
| Shaft end | Plain shaft |
| Encoder system | Encoder AS24DQI: absolute encoder single-turn 24 bits |

SIEMENS

**MLFB-Ordering data** **1FK7100-2AF71-1BG2**



Figure similar

## Optimum operating point

| | |
|---|---|
| Optimum speed | 3000 rpm |
| Optimum power | 3.8 kW |

## Limiting data

| | |
|---|---|
| Max. permissible speed (mech.) | 5000 rpm |
| Max. permissible speed (inverter) | 5000 rpm |
| Maximum torque | 55.0 Nm |
| Maximum current | 37.0 A |

## Recommended Motor Module

| | |
|---|---|
| Rated inverter current | 18 A |
| Maximum inverter current | 54 A |
| Maximum torque | 55.00 Nm |