

Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data 1FK7100-2AF71-1CB2

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Engineering data		Mechanical data	
Rated speed (100 K)	3000 rpm	Motor type	Permanent-magnet synchronous motor
Number of poles	8	Motor type	Compact
Rated torque (100 K)	12.0 Nm	Shaft height	100
Rated current	8.0 A	Cooling	Natural cooling
Static torque (60 K)	14.90 Nm	Radial runout tolerance	0.050 mm
Static torque (100 K)	18.00 Nm	Concentricity tolerance	0.10 mm
Stall current (60 K)	9.00 A	Axial runout tolerance	0.10 mm
Stall current (100 K)	11.10 A	Vibration severity grade	Grade A
Moment of inertia	62.000 kgcm ²	Connector size	1
Efficiency	92.0 %	Degree of protection	IP65 and DE flange IP67
Physical constants		Design acc. to Code I	IM B5 (IM V1, IM V3)
Torque constant	1.62 Nm/A	Temperature monitoring	Pt1000 temperature sensor
Voltage constant at 20° C	104.5 V/1000*min ⁻¹	Electrical connectors	Connectors for signals and power rotatable
Winding resistance at 20° C	0.32 Ω	Color of the housing	Standard (Anthracite RAL 7016)
Rotating field inductance	7.3 mH	Holding brake	with holding brake
Electrical time constant	22.50 ms	Shaft end	Feather key
Mechanical time constant	2.00 ms	Encoder system	Encoder AM24DQI: absolute encoder 24 bits (resolution 16777216, encoder-internal 2048 S/R) + 12 bits multi-turn (traversing range 4096 revolutions)
Thermal time constant	55 min		
Shaft torsional stiffness	135000 Nm/rad		
Net weight of the motor	21.0 kg		



Figure similar

MLFB-Ordering data 1FK7100-2AF71-1CB2

Optimum operating point		Recommended Motor Module	
Optimum speed	3000 rpm	Rated inverter current	18 A
Optimum power	3.8 kW	Maximum inverter current	54 A
Limiting data		Maximum torque	55.00 Nm
Max. permissible speed (mech.)	5000 rpm		
Max. permissible speed (inverter)	5000 rpm		
Maximum torque	55.0 Nm		
Maximum current	37.0 A		
Holding brake			
Holding brake version	Permanent-magnet brake		
Holding torque	23.0 Nm		
Power supply voltage	DC 24 V ± 10 %		
Coil current	1.0 A		
Opening time	300 ms		
Closing time	70 ms		
Highest braking work	3380 J		