

Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data                      1FK7101-3BF71-1QB0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

| Engineering data            |                               | Mechanical data          |                                                       |
|-----------------------------|-------------------------------|--------------------------|-------------------------------------------------------|
| Rated speed (100 K)         | 3000 rpm                      | Motor type               | Permanent-magnet synchronous motor                    |
| Number of poles             | 8                             | Motor type               | High Inertia                                          |
| Rated torque (100 K)        | 15.5 Nm                       | Shaft height             | 100                                                   |
| Rated current               | 11.6 A                        | Cooling                  | Natural cooling                                       |
| Static torque (60 K)        | 22.50 Nm                      | Radial runout tolerance  | 0.050 mm                                              |
| Static torque (100 K)       | 27.00 Nm                      | Concentricity tolerance  | 0.10 mm                                               |
| Stall current (60 K)        | 15.20 A                       | Axial runout tolerance   | 0.10 mm                                               |
| Stall current (100 K)       | 18.80 A                       | Vibration severity grade | Grade A                                               |
| Moment of inertia           | 136.000 kgcm²                 | Connector size           | 1.5                                                   |
| Efficiency                  | 92.0 %                        | Degree of protection     | IP64                                                  |
| Physical constants          |                               | Design acc. to Code I    | IM B5 (IM V1, IM V3)                                  |
| Torque constant             | 1.44 Nm/A                     | Temperature monitoring   | Pt1000 temperature sensor                             |
| Voltage constant at 20° C   | 92.5 V/1000*min <sup>-1</sup> | Electrical connectors    | Connectors for signals and power rotatable            |
| Winding resistance at 20° C | 0.14 Ω                        | Color of the housing     | Standard (Anthracite RAL 7016)                        |
| Rotating field inductance   | 3.5 mH                        | Holding brake            | with holding brake                                    |
| Electrical time constant    | 25.00 ms                      | Shaft end                | Feather key                                           |
| Mechanical time constant    | 2.61 ms                       | Encoder system           | Encoder AS20DQI: absolute encoder single-turn 20 bits |
| Thermal time constant       | 60 min                        |                          |                                                       |
| Shaft torsional stiffness   | 116000 Nm/rad                 |                          |                                                       |
| Net weight of the motor     | 30.2 kg                       |                          |                                                       |



Figure similar

MLFB-Ordering data                      1FK7101-3BF71-1QB0

| Optimum operating point           |                        | Recommended Motor Module |          |
|-----------------------------------|------------------------|--------------------------|----------|
| Optimum speed                     | 3000 rpm               | Rated inverter current   | 18 A     |
| Optimum power                     | 4.8 kW                 | Maximum inverter current | 54 A     |
| Limiting data                     |                        | Maximum torque           | 72.00 Nm |
| Max. permissible speed (mech.)    | 5000 rpm               |                          |          |
| Max. permissible speed (inverter) | 5000 rpm               |                          |          |
| Maximum torque                    | 80.0 Nm                |                          |          |
| Maximum current                   | 63.0 A                 |                          |          |
| Holding brake                     |                        |                          |          |
| Holding brake version             | Permanent-magnet brake |                          |          |
| Holding torque                    | 43.0 Nm                |                          |          |
| Power supply voltage              | DC 24 V ± 10 %         |                          |          |
| Coil current                      | 1.0 A                  |                          |          |
| Opening time                      | 300 ms                 |                          |          |
| Closing time                      | 70 ms                  |                          |          |
| Highest braking work              | 3380 J                 |                          |          |