

Article No. : 1FK2103-2AH01-0SA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Basic motor data	
Motor type	Permanent-magnet synchronous motor, Natural cooling, IP65
Motor type	High Dynamic
Static torque	0.64 Nm
Static current	1.1 A
Maximum torque	1.95 Nm
Maximum current	4.0 A
Maximum speed	8,000 rpm
Rotor moment of inertia	0.0930 kgcm ²
Weight	1.2 kg

Rated data	
SINAMICS S210, 3AC 400V	
Rated speed	4,500 rpm
Rated torque	0.59 Nm
Rated current	1.1 A
Rated power	0.28 kW

Encoder system	
Encoder system	Encoder AS22DQC: Absolute encoder single turn 22 bit

Motor connection	
Connection type	OCC for S210
Connector size	M17

Mechanical data	
Design acc. to Code I	IM B5 (IM V1, IM V3)
Vibration severity grade	Grade A
Shaft height	30
Flange size (AB)	60 mm
Centering ring (N)	50 mm
Hole circle (M)	70 mm
Screw-on hole (S)	5.4 mm
Overall length (LB)	99 mm
Diameter of shaft (D)	14 mm
Length of shaft (E)	30 mm
Length of flange diagonal (P)	81 mm
Shaft end	Plain shaft
Color of the housing	Standard (Anthracite, similar to RAL 7016)

