

Article No. : 1FK2104-5AK10-2MA0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :



Figure similar

Item no. :  
Consignment no. :  
Project :

| Basic motor data        |   |
|-------------------------|---|
| Motor type              | Permanent-magnet synchronous motor, Natural cooling, IP64 |
| Motor type              | High Dynamic  |
| Static torque           | 2.40 Nm   |
| Static current          | 4.4 A   |
| Maximum torque          | 7.60 Nm   |
| Maximum current         | 16.0 A  |
| Maximum speed           | 8,000 rpm   |
| Rotor moment of inertia | 0.6500 kgcm <sup>2</sup>                                  |
| Weight                  | 3.7 kg  |

| Rated data              |           |
|-------------------------|-----------|
| SINAMICS S210, 3AC 400V |           |
| Rated speed             | 6,000 rpm |
| Rated torque            | 1.70 Nm   |
| Rated current           | 3.2 A     |
| Rated power             | 1.07 kW   |

| Encoder system |   |
|----------------|---|
| Encoder system | Encoder AM22DQC: Absolute encoder 22 bit + 12 bit multiturn |

| Motor connection |              |
|------------------|--------------|
| Connection type  | OCC for S210 |
| Connector size   | M17          |

| Mechanical data               |  |
|-------------------------------|--|
| Design acc. to Code I         | IM B5 (IM V1, IM V3)                       |
| Vibration severity grade      | Grade A                                    |
| Shaft height                  | 40   |
| Flange size (AB)              | 80 mm                                      |
| Centering ring (N)            | 70 mm                                      |
| Hole circle (M)               | 90 mm                                      |
| Screw-on hole (S)             | 6.5 mm                                     |
| Overall length (LB)           | 170 mm                                     |
| Diameter of shaft (D)         | 14 mm                                      |
| Length of shaft (E)           | 30 mm                                      |
| Length of flange diagonal (P) | 105 mm                                     |
| Shaft end                     | Plain shaft                                |
| Color of the housing          | Standard (Anthracite, similar to RAL 7016) |



| Holding brake                                  |           |
|--|-----------|
| Holding torque                                 | 3.30 Nm   |
| Average dynamic torque                         | 3.30 Nm   |
| Opening time                                   | 50 ms     |
| Closing time                                   | 40 ms     |
| Maximum single switching energy <sup>1)</sup>  | 270 J     |
| Service life, operating energy                 | 120,000 J |
| Holding current <sup>2)</sup>                  | 0.2 A     |
| Break-induced current for 500 ms <sup>2)</sup> | 1.2 A     |

<sup>1)</sup>Up to three consecutive emergency stops and up to 25% of all emergency stops as a Wmax high energy stop possible.  
<sup>2)</sup>Typical value for 20°C ambient temperature. At -15°C the break-induced currents can be increased by up to 30%.