

Data sheet for SIMOTICS S-1FK2

Article No. : 1FK2203-2AK10-1SA0

Client order no. :
Order no. :
Offer no. :
Remarks :



Figure similar

Item no. :
Consignment no. :
Project :

Basic motor data	
Motor type	Permanent-magnet synchronous motor, Natural cooling, IP64
Motor type	Compact
Static torque	0.64 Nm
Static current	1.1 A
Maximum torque	1.85 Nm
Maximum current	3.4 A
Maximum speed	8,000 rpm
Rotor moment of inertia	0.2200 kgcm ²
Weight	1.5 kg

Rated data	
SINAMICS S210, 3AC 400V	
Rated speed	6,000 rpm
Rated torque	0.41 Nm
Rated current	0.8 A
Rated power	0.26 kW

Encoder system	
Encoder system	Encoder AS22DQC: Absolute encoder single turn 22 bit

Motor connection	
Connection type	OCC for S210
Connector size	M17

Mechanical data	
Design acc. to Code I	IM B5 (IM V1, IM V3)
Vibration severity grade	Grade A
Shaft height	30
Flange size (AB)	60 mm
Centering ring (N)	50 mm
Hole circle (M)	70 mm
Screw-on hole (S)	5.4 mm
Overall length (LB)	131 mm
Diameter of shaft (D)	14 mm
Length of shaft (E)	30 mm
Length of flange diagonal (P)	81 mm
Shaft end	Fitted key
Color of the housing	Standard (Anthracite, similar to RAL 7016)



Holding brake	
Holding torque	1.30 Nm
Average dynamic torque	1.30 Nm
Opening time	40 ms
Closing time	30 ms
Maximum single switching energy ¹⁾	62 J
Service life, operating energy	17,500 J
Holding current ²⁾	0.15 A
Break-induced current for 500 ms ²⁾	0.8 A

¹⁾Up to three consecutive emergency stops and up to 25% of all emergency stops as a Wmax high energy stop possible.
²⁾Typical value for 20°C ambient temperature. At -15°C the break-induced currents can be increased by up to 30%.