Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1AV2116A SIMOTICS GP - 112 M - IM B5 - 2p Offer no. Client order no. Item-No Order no. Consignment no. Project Remarks Safe Area **Electrical data** -/η 3) Δ/Υ U f Р Р ī М cosφ 3) I_A/I_N M_A/M_N M_K/M_N IE-CL n [V] [Hz] [kW] [hp] [A] [1/min] [Nm] 4/4 3/4 4/4 I_I/I_N T_I/T_N T_B/T_N 3/4 2/4 **DOL duty (S1)** - 155(F) to 130(B) 460 Δ 60 5.50 -/-9.00 3550 14.8 88.5 88.6 87.4 0.87 0.83 0.74 9.9 2.8 4.5 IE2 IM B5 / IM 3001 FS 112 M UKCA IEC/EN 60034 IEC, DIN, ISO, VDE, EN Environmental conditions: -20 °C - +40 °C / 1000 m Locked rotor time (hot / cold): 5.8 s | 9.8 s Mechanical data 69 / 81 dB(A) 2) 3) Sound level (SPL / SWL) at 50Hz|60Hz 73 / 85 dB(A) 2) 3) Vibration severity grade Α 0.0120 kg m² Moment of inertia Thermal class F Bearing DE | NDE 6206 2Z C3 6206 2Z C3 Duty type S1 bearing lifetime Direction of rotation bidirectional $L_{10mh}\,F_{Rad\,\,min}$ for coupling operation $50|60Hz^{\,1)}$ 40000 h 32000 h Frame material aluminum Regreasing device Without Net weight of the motor (IM B3) 34 kg Coating (paint finish) Standard paint finish C2 Grease nipple Preloaded bearing DE RAL7030 Type of bearing Color, paint shade Condensate drainage holes Without Motor protection (A) without (Standard) External earthing terminal Without Method of cooling IC411 - self ventilated, surface cooled Terminal box Terminal box position top Max. cross-sectional area 4 mm² Material of terminal box Aluminium Cable diameter from ... to ... 11 mm - 21 mm Type of terminal box TB1 F00 2xM32x1,5 Cable entry Contact screw thread Μ4 Cable gland 2 plugs 1) L_{10mh} according to DIN ISO 281 10/2010 3) Value is valid only for DOL operation with motor design IC411 IA/IN = locked rotor current / current nominal M_A/M_N = locked rotor torque / torque nominal 2) at rated power / at full load M_K/M_N = break down torque / nominal torque Transmittal, reproduction, dissemination and/or editing of this document as well as utilization of its contents and communication thereof to others without express authorization are prohibited. Offenders will be held liable for payment of damages. All rights created by patent grant or registration of a utility model or design patent are reserved. Responsible department Technical reference Created by Approved by Technical data are subject to change! There may be discrepancies between calculated and rating plate IN LVM SPC Created automatically Document type Document status Released Technical data sheet **SIEMENS** Document number 1LE1001-1BA69-0FA4 TDS-240504-140557 M2F Revision Creation date Language Page Restricted © Innomotics 2024 2024-05-04

Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1AV2116A			SIMOTICS GF	SIMOTICS GP - 112 M - IM B5 - 2p						
Special de	esign									
M2F	460 VD for 60 Hz, 50-	-Hz power								
Transmittal, ı	reproduction, dissemination and	d/or editing of this document as we	Il as utilization of its contents and	communication thereof to others	without exp	oress authoriza	tion are prohibited. Offenders v	vill be held liable	for payment of	
			ights created by patent grant or re				·			
Responsible d	lenartment	Technical reference	Created by	Approved by	Technical	data are sub	iect to change! There may be	Link docum	ents	
IN LVM	repartment	reclinical reference	SPC	Created automatically	discrepan		calculated and rating plate	LITIK GOCUM	**************************************	
		Document type	J 5. C	a. cuted dutomatically	values.	Document	status			
	MENS	Technical data sheet			Released		300			
SIE			Document title			Document number				
		1LE1001-1BA69-0FA	\4				504-140557	直接		
Restricted		M2F			ŀ	Revision	Creation date	Language	Page	
© Innomo	tics 2024					AA	2024-05-04	en	2/2	