

Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1AV3094C SIMOTICS GP - 90 L - IM B3 - 6p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	Project

Remarks

Safe Area

Electrical data -/-

U	Δ / Y	f	P	P	I	n	M	η ³⁾			cosφ ³⁾			I _A /I _N	M _A /M _N	M _K /M _N	IE-CL
[V]		[Hz]	[kW]	[hp]	[A]	[1/min]	[Nm]	4/4	3/4	2/4	4/4	3/4	2/4	I _I /I _N	T _I /T _N	T _B /T _N	
DOL duty (S1) - 155(F) to 130(B)																	
230	Δ	50	1.10	-/-	5.20	950	11.1	81.0	81.4	79.3	0.66	0.57	0.44	5.0	2.8	3.0	IE3
400	Y	50	1.10	-/-	2.95	950	11.1	81.0	81.4	79.3	0.66	0.57	0.44	5.0	2.8	3.0	IE3
IM B3 / IM 1001			FS 90 L				IP55	UKCA		IEC/EN 60034		IEC, DIN, ISO, VDE, EN					
Environmental conditions : -20 °C - +40 °C / 1000 m									Locked rotor time (hot / cold) : 31.8 s 40.5 s								

Mechanical data				
Sound level (SPL / SWL) at 50Hz 60Hz	43 / 55 dB(A) ^{2) 3)}	46 / 58 dB(A) ^{2) 3)}	Vibration severity grade	A
Moment of inertia	0.0052 kg m²		Thermal class	F
Bearing DE NDE	6205 2Z C3	6004 2Z C3	Duty type	S1
bearing lifetime			Direction of rotation	bidirectional
L _{10mh} F _{Rad min} for coupling operation 50 60Hz ¹⁾	40000 h	32000 h	Frame material	aluminum
Regreasing device	Without		Net weight of the motor (IM B3)	19 kg
Grease nipple	-/-		Coating (paint finish)	Standard paint finish C2
Type of bearing	Preloaded bearing DE		Color, paint shade	RAL7030
Condensate drainage holes	Without		Motor protection	(B) 1 PTC thermistor - for tripping (2 terminals)
External earthing terminal	Without		Method of cooling	IC411 - self ventilated, surface cooled



Terminal box			
Terminal box position	top	Max. cross-sectional area	1.5 mm²
Material of terminal box	Aluminium	Cable diameter from ... to ...	9 mm - 17 mm
Type of terminal box	TB1 E00	Cable entry	1xM25x1,5-1xM16x1,5
Contact screw thread	M4	Cable gland	2 plugs

I_A/I_N = locked rotor current / current nominal 1) L_{10mh} according to DIN ISO 281 10/2010 3) Value is valid only for DOL operation with motor design IC411

M_A/M_N = locked rotor torque / torque nominal 2) at rated power / at full load

M_K/M_N = break down torque / nominal torque

Transmittal, reproduction, dissemination and/or editing of this document as well as utilization of its contents and communication thereof to others without express authorization are prohibited. Offenders will be held liable for payment of damages. All rights created by patent grant or registration of a utility model or design patent are reserved.

Responsible department IN LVM		Technical reference	Created by SPC	Approved by Created automatically	Technical data are subject to change! There may be discrepancies between calculated and rating plate values.		Link documents	
		Document type Technical data sheet			Document status Released			
		Document title 1LE1003-0EC42-2AB4			Document number TDS-240427-191235			
		Restricted © Innomotics 2024			Revision AA	Creation date 2024-04-27	Language en	