

Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1AV2063B

SIMOTICS GP - 63 M - IM B3 - 4p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	Project

Remarks

Safe Area

-/-

U	Δ / Y	f	P	P	I	n	M	η ³⁾			cosφ ³⁾			I _A /I _N	M _A /M _N	M _K /M _N	IE-CL
[V]		[Hz]	[kW]	[hp]	[A]	[1/min]	[Nm]	4/4	3/4	2/4	4/4	3/4	2/4	I _I /I _N	T _I /T _N	T _B /T _N	
DOL duty (S1) - 155(F) to 130(B)																	
230	Δ	50	0.18	-/-	1.07	1385	1.2	64.7	62.4	55.7	0.65	0.56	0.44	3.3	2.6	2.6	IE2
400	Y	50	0.18	-/-	0.62	1385	1.2	64.7	62.4	55.7	0.65	0.56	0.44	3.3	2.6	2.6	IE2
460	Y	60	0.21	-/-	0.60	1685	1.2	68.0	65.8	59.7	0.65	0.56	0.45	3.8	2.8	2.9	IE2
460	Y	60	0.18	-/-	0.56	1710	1.0	68.0	64.4	57.3	0.59	0.50	0.40	3.9	3.3	3.4	IE2
IM B3 / IM 1001		FS 63 M				IP55	UKCA	IEC/EN 60034		IEC, DIN, ISO, VDE, EN							
Environmental conditions : -20 °C - +40 °C / 1000 m									Locked rotor time (hot / cold) : 36.3 s 47.7 s								

Mechanical data																	
Sound level (SPL / SWL) at 50Hz 60Hz						/ dB(A) ^{2) 3)}			/ dB(A) ^{2) 3)}			Vibration severity grade					
Moment of inertia						0.0004 kg m²						Thermal class					
Bearing DE NDE						6201 2Z C3			6201 2Z C3			Duty type					
bearing lifetime												Direction of rotation					
L _{10mh} F _{Rad min} for coupling operation						40000 h			32000 h			Frame material					
50 60Hz ¹⁾												aluminum					
Regreasing device						Without						Net weight of the motor (IM B3)					
Grease nipple						-/-						Coating (paint finish)					
Type of bearing						Preloaded bearing DE						Color, paint shade					
Condensate drainage holes						Without						Motor protection					
External earthing terminal						Without						Method of cooling					
												IC411 - self ventilated, surface cooled					

Terminal box			
Terminal box position	top	Max. cross-sectional area	1.5 mm²
Material of terminal box	Aluminium	Cable diameter from ... to ...	9 mm - 17 mm
Type of terminal box	TB1 B00	Cable entry	1xM25x1,5
Contact screw thread	M4	Cable gland	1 plug