

SIMOTICS GP - 80 M - IM B14 - 4p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	Project

Safe Area

-/-

U	Δ / Y	f	P	P	I	n	M	η ³⁾			cosφ ³⁾			I _A /I _N	M _A /M _N	M _K /M _N	IE-CL
[V]		[Hz]	[kW]	[hp]	[A]	[1/min]	[Nm]	4/4	3/4	2/4	4/4	3/4	2/4	I _I /I _N	T _I /T _N	T _B /T _N	
DOL duty (S1) - 155(F) to 130(B)																	
230	Δ	50	0.55	-/-	2.40	1440	3.6	77.1	76.8	73.7	0.74	0.65	0.51	5.3	2.2	3.1	IE2
400	Y	50	0.55	-/-	1.39	1440	3.6	77.1	76.8	73.7	0.74	0.65	0.51	5.3	2.2	3.1	IE2
460	Y	60	0.63	-/-	1.42	1735	3.5	75.5	75.8	73.5	0.74	0.67	0.54	5.7	2.4	3.3	IE2
460	Y	60	0.55	-/-	1.29	1750	3.0	75.5	74.6	71.1	0.71	0.62	0.49	6.4	2.7	3.8	IE2
IM B14 / IM 3601			FS 80 M			IP55	UKCA	IEC/EN 60034		IEC, DIN, ISO, VDE, EN							
Environmental conditions : -20 °C - +40 °C / 1000 m									Locked rotor time (hot / cold) : 17.8 s 23.3 s								

Sound level (SPL / SWL) at 50Hz 60Hz	53 / 64 dB(A) ^{2) 3)}	55 / 66 dB(A) ^{2) 3)}	Vibration severity grade	A
Moment of inertia	0.0017 kg m²		Thermal class	F
Bearing DE NDE	6004 2Z C3	6004 2Z C3	Duty type	S1
bearing lifetime			Direction of rotation	bidirectional
L _{10mh} F _{Rad min} for coupling operation 50 60Hz ¹⁾	40000 h	32000 h	Frame material	aluminum
Regreasing device	Without		Net weight of the motor (IM B3)	10 kg
Grease nipple	-/-		Coating (paint finish)	Standard paint finish C2
Type of bearing	Preloaded bearing DE		Color, paint shade	RAL7030
Condensate drainage holes	Without		Motor protection	(A) without (Standard)
External earthing terminal	Without		Method of cooling	IC411 - self ventilated, surface cooled

Terminal box position	top	Max. cross-sectional area	1.5 mm²
Material of terminal box	Aluminium	Cable diameter from ... to ...	9 mm - 17 mm
Type of terminal box	TB1 E00	Cable entry	1xM25x1,5
Contact screw thread	M4	Cable gland	1 plug

3) Value is valid only for DOL operation with motor design IC411

Transmittal, reproduction, dissemination and/or editing of this document as well as utilization of its contents and communication thereof to others without express authorization are prohibited. Offenders will be held liable for payment of damages. All rights created by patent grant or registration of a utility model or design patent are reserved.

Responsible department IN LVM	Technical reference	Created by SPC	Approved by Created automatically	Technical data are subject to change! There may be discrepancies between calculated and rating plate values.		Link documents	
SIEMENS	Document type Technical data sheet			Document status Released			
	Document title 1LE1001-0DB22-2KA4			Document number TDS-240505-073955			
Restricted © Innomotics 2024				Revision AA	Creation date 2024-05-05	Language en	Page 1/1