

SIMOTICS GP - 160 L - IM B5 - 4p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	Project

Safe Area

-/-

U	Δ / Y	f	P	P	I	n	M	η ³⁾			cosφ ³⁾			I _A /I _N	M _A /M _N	M _K /M _N	IE-CL
[V]		[Hz]	[kW]	[hp]	[A]	[1/min]	[Nm]	4/4	3/4	2/4	4/4	3/4	2/4	I _I /I _N	T _I /T _N	T _B /T _N	
DOL duty (S1) - 155(F) to 130(B)																	
400	Δ	50	15.00	-/-	28.50	1465	98.0	92.1	92.7	92.0	0.83	0.78	0.67	7.9	2.8	3.4	IE3
690	Y	50	15.00	-/-	16.40	1465	98.0	92.1	92.7	92.0	0.83	0.78	0.67	7.9	2.8	3.4	IE3
460	Δ	60	17.30	-/-	28.50	1765	94.0	92.4	92.5	92.0	0.83	0.79	0.69	7.9	2.7	3.3	IE2
460	Δ	60	15.00	-/-	25.00	1775	81.0	93.0	92.9	92.1	0.81	0.75	0.64	8.9	3.1	3.8	IE3
IM B5 / IM 3001			FS 160 L			IP55	UKCA	IEC/EN 60034		IEC, DIN, ISO, VDE, EN							
Environmental conditions : -20 °C - +40 °C / 1000 m									Locked rotor time (hot / cold) : 24.6 s 33.3 s								

Sound level (SPL / SWL) at 50Hz 60Hz	58 / 66 dB(A) ^{2) 3)}	66 / 74 dB(A) ^{2) 3)}	Vibration severity grade	A
Moment of inertia	0.0890 kg m²		Thermal class	F
Bearing DE NDE	6209 2Z C3	6209 2Z C3	Duty type	S1
bearing lifetime			Direction of rotation	bidirectional
L _{10mh} F _{Rad min} for coupling operation 50 60Hz ¹⁾	40000 h	32000 h	Frame material	aluminum
Regreasing device	Without		Net weight of the motor (IM B3)	106 kg
Grease nipple	-/-		Coating (paint finish)	Standard paint finish C2
Type of bearing	Locating bearing NDE		Color, paint shade	RAL7030
Condensate drainage holes	Without		Motor protection	(B) 3 PTC thermistors - for tripping (2 terminals)
External earthing terminal	Without		Method of cooling	IC411 - self ventilated, surface cooled

Terminal box position	top	Max. cross-sectional area	16 mm²
Material of terminal box	Aluminium	Cable diameter from ... to ...	19 mm - 28 mm
Type of terminal box	TB1 J00	Cable entry	2xM40x1,5-1xM16x1,5
Contact screw thread	M5	Cable gland	3 plugs

3) Value is valid only for DOL operation with motor design IC411

Transmittal, reproduction, dissemination and/or editing of this document as well as utilization of its contents and communication thereof to others without express authorization are prohibited. Offenders will be held liable for payment of damages. All rights created by patent grant or registration of a utility model or design patent are reserved.

Responsible department IN LVM	Technical reference	Created by SPC	Approved by Created automatically	Technical data are subject to change! There may be discrepancies between calculated and rating plate values.		Link documents	
	Document type Technical data sheet			Document status Released			
	Document title 1LE1003-1DB43-4FB4			Document number TDS-240503-021819			
Restricted © Innomotics 2024				Revision AA	Creation date 2024-05-03	Language en	Page 1/1