Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



SIMOTICS GP - 160 L - IM B3 - 6p Motor type : 1AV3164C Offer no. Client order no. Item-No Order no. Consignment no. Project Remarks Safe Area **Electrical data** -/-Δ/Υ U f Р Р ī М η 3) cosφ ³⁾ I_A/I_N M_A/M_N M_K/M_N IE-CL n [V] [Hz] [kW] [hp] [A] [1/min] [Nm] 4/4 3/4 4/4 I_I/I_N T_I/T_N T_B/T_N 2/4 3/4 2/4 **DOL duty (S1)** - 155(F) to 130(B) 400 Δ 50 11.00 22.00 980 107.0 90.3 90.7 89.8 0.80 0.75 0.64 6.8 2.9 2.8 IE3 690 11.00 -/-12.70 107.0 0.75 2.9 2.8 50 980 90.3 90.7 89.8 0.80 0.64 6.8 IE3 IM B3 / IM 1001 FS 160 L IP55 UKCA IEC/EN 60034 IEC, DIN, ISO, VDE, EN Environmental conditions: -20 °C - +40 °C / 1000 m Locked rotor time (hot / cold): 17.9 s | 25.4 s Mechanical data 67 / 79 dB(A) 2) 3) Sound level (SPL / SWL) at 50Hz|60Hz 70 / 82 dB(A) 2) 3) Vibration severity grade Α 0.1640 kg m² Moment of inertia Thermal class F Bearing DE | NDE S1 6209 2Z C3 6209 2Z C3 Duty type bearing lifetime Direction of rotation bidirectional $L_{10mh}\,F_{Rad\,\,min}$ for coupling operation $50|60Hz^{\,1)}$ 40000 h 32000 h Frame material aluminum Regreasing device Without Net weight of the motor (IM B3) 115 kg Coating (paint finish) Standard paint finish C2 Grease nipple Locating bearing NDE Color, paint shade RAL7030 Type of bearing Condensate drainage holes Without Motor protection (B) 3 PTC thermistors - for tripping (2 terminals) External earthing terminal Without Method of cooling IC411 - self ventilated, surface cooled Terminal box Terminal box position top Max. cross-sectional area $16 \, mm^2$ Material of terminal box Aluminium Cable diameter from ... to ... 19 mm - 28 mm Type of terminal box TB1 J00 2xM40x1,5-1xM16x1,5 Cable entry Contact screw thread М5 Cable gland 3 plugs 1) L_{10mh} according to DIN ISO 281 10/2010 3) Value is valid only for DOL operation with motor design IC411 IA/IN = locked rotor current / current nominal 2) at rated power / at full load M_A/M_N = locked rotor torque / torque nominal M_K/M_N = break down torque / nominal torque Transmittal, reproduction, dissemination and/or editing of this document as well as utilization of its contents and communication thereof to others without express authorization are prohibited. Offenders will be held liable for payment of damages. All rights created by patent grant or registration of a utility model or design patent are reserved. Responsible department Technical reference Created by Approved by Technical data are subject to change! There may be discrepancies between calculated and rating plate IN LVM SPC Created automatically Document type Document status Released Technical data sheet **SIEMENS** Document number 1LE1003-1DC43-4AB4 TDS-240502-022759

Revision

Creation date

2024-05-02

Language

Page

1/1

© Innomotics 2024

Restricted