

Data sheet for three-phase Squirrel-Cage-Motors ABB

Motor type:	FS: 444TS - p - 125 hp -
-------------	--------------------------

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	Project

Remarks

Electrical data	
-----------------	--

[illegible]

Frame Type: 444TS	Type of constr.:		Motor Prot.:	NEMA Des.:	S.F.: 1.15
Mtr. WT: lbs	Insulation Class.:Standard Class F Insulation	Temp. Rise Cl.: B	Amb. Temp.: + 40 to -20 °C @1000 m	kVA:	IP 54

Mechanical data

Sound level (SPL / SWL) at 60 Hz				dB(A) / dB(A)				Thickener	
Octave Band Center Frequencies Hertz								Safe Stall Time Hot	
250	500	1000	2000	4000	8000	Hz		s	
SPL@3								dB(A)	
Moment of inertia								Lb-ft²	
Ext Load Inertia Capability:								Lb ft²	
Bearings									
Bearing DE NDE									
Bearing_Type								Ball Bearing	
AFBMA:									
Grease									
Capacity								oz	
Grease Type:									

Terminal box


Lead Wire Connection					Terminal box position
Voltage	L1	L2	L3	Connected together	Material of terminal box
					Cable entry
					-/-

Notes:

I_{r}/I_{N} = locked rotor current / current nominal M_{r}/M_{N} = locked rotor torque / torque nominal M_{b}/M_{N} = break down torque / nominal torque	3) Value is valid only for DOL operation with motor design IC411 2) at rated power / at full load
--	--


I_{r}/I_{N} = locked rotor current / current nominal M_{r}/M_{N} = locked rotor torque / torque nominal M_{b}/M_{N} = break down torque / nominal torque	3) Value is valid only for DOL operation with motor design IC411 2) at rated power / at full load
--	--

Responsible department IN LVM	Technical reference	Created by SPC	Approved by	<i>Technical data are subject to change! There may be discrepancies</i>
----------------------------------	---------------------	-------------------	-------------	---

	Document type	Document status		customer	
	Datasheet	Released			
© ABB 2024	Document title	Document number		Language	Page
	1LE2221-4DB1.-....	Revision	Creation date		
		01	2024-05-05 09:09	en	1/1

Main terminal diagram

Transmittal, reproduction, dissemination and/or editing of this document as well as utilization of its contents and communication thereof to others without express authorization are prohibited. Offenders will be held liable for payment of damages. All rights created by patent grant or registration of a utility model or design patent are reserved.

Responsible department IN LVM	Technical reference	Created by	Approved by Created automatically	Technical data are subject to change! There may be discrepancies between calculated and rating plate values.		Link documents	
	Document type Wiring diagramm			Document status Released			
	Document title 1LE2221-4DB1.-....			Document number WDS-240505-090902			
Restricted © Innomotics 2024				Revision AA	Creation date 2024-05-05	Language en	Page 1/1