

Data sheet for three-phase Squirrel-Cage-Motors ABB

Motor type: FS: 324T - p - 20 hp -

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	Project
Remarks		

Electrical data

U [V]	Δ / Y	f [Hz]	P [HP]	P [kW]	n [rpm]	I Load [Amps]					LRC	Nom. Eff Load [%]			Pwr. Factor Load [%]			Torque [lb-ft]	T <sub>A</sub> /T <sub>N</sub> LRT [%]	T <sub>k</sub> /T <sub>N</sub> BDT [%]
						4/4	3/4	1/2	0	4/4		3/4	2/4	4/4	3/4	2/4				
		60	20.00	15.00																
Frame Type: 324T			Type of constr.:								Motor Prot.:			NEMA Des.:			S.F.: 1.15			
Mtr. WT: lbs			Insulation Class.:Standard Class F Insulation							Temp. Rise Cl.: B		Amb. Temp.: + 40 to -20 °C @1000 m			kVA:			IP 55		


Mechanical data

Sound level (SPL / SWL) at 60 Hz							dB(A) / dB(A)		Thickener	
Octave Band Center Frequencies Hertz									Safe Stall Time Hot	
250     500     1000     2000     4000     8000							Hz		Safe Stall Time Cold	
SPL@3							dB(A)		Frame material	
Moment of inertia							Lb-ft²		Color, paint shade	
Ext Load Inertia Capability:							Lb ft²		Coating (paint finish)	
Bearings									Ventilation Type	
Bearing DE   NDE									Method of cooling	
Bearing_Type							Ball Bearing		Direction of rotation	
AFBMA:									Fan Material	
Grease									VFD	
Capacity							oz		Space heaters	
Grease Type:									Brake:	
									Standard Paint - RAL7030	
									Standard Alkyed + Epoxy (C2)	

Terminal box


Lead Wire Connection					Terminal box position				
Voltage	L1	L2	L3	Connected together	Material of terminal box				
					Cable entry				

<b>Notes:</b>									
I <sub>L</sub> /I <sub>N</sub> = locked rotor current / current nominal					3) Value is valid only for DOL operation with motor design IC411				
M <sub>L</sub> /M <sub>N</sub> = locked rotor torque / torque nominal					2) at rated power / at full load				
M <sub>b</sub> /M <sub>N</sub> = break down torque / nominal torque									

Responsible department IN LVM		Technical reference		Created by SPC		Approved by		Technical data are subject to change! There may be discrepancies between the data in this document and the actual product.					
		Document type Datasheet		Document status Released				customer					
		Document title 1LE2321-3AD1.-....				Document number							
		© ABB 2024						Revision 01		Creation date 2024-05-05 00:30		Language en	

Main terminal diagram

Transmittal, reproduction, dissemination and/or editing of this document as well as utilization of its contents and communication thereof to others without express authorization are prohibited. Offenders will be held liable for payment of damages. All rights created by patent grant or registration of a utility model or design patent are reserved.

Responsible department IN LVM	Technical reference	Created by	Approved by Created automatically	Technical data are subject to change! There may be discrepancies between calculated and rating plate values.		<a href="#">Link documents</a>	
	Document type Wiring diagramm			Document status Released			
	Document title 1LE2321-3AD1.-....			Document number WDS-240505-003051			
Restricted © Innomotics 2024				Revision AA	Creation date 2024-05-05	Language en	Page 1/1