

SIMOTICS SD - 225 M - IM B3 - 2p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	Project

Safe Area

-/-

U	Δ / Y	f	P	P	I	n	M	η ³⁾			cosφ ³⁾			I _A /I _N	M _A /M _N	M _K /M _N	IE-CL
[V]		[Hz]	[kW]	[hp]	[A]	[1/min]	[Nm]	4/4	3/4	2/4	4/4	3/4	2/4	I _I /I _N	T _I /T _N	T _B /T _N	
DOL duty (S1) - 155(F) to 130(B)																	
400	Δ	50	45.00	-/-	80.00	2960	145.0	91.7	92.0	91.6	0.88	0.85	0.78	6.7	2.3	3.0	IE1
690	Y	50	45.00	-/-	46.50	2960	145.0	91.7	92.0	91.6	0.88	0.85	0.78	6.7	2.3	3.0	IE1
460	Δ	60	51.00	-/-	78.00	3560	137.0	92.4	92.4	91.7	0.89	0.87	0.80	6.7	2.3	3.0	IE1
IM B3 / IM 1001			FS 225 M			IP55	UKCA	IEC/EN 60034		IEC, DIN, ISO, VDE, EN							
Environmental conditions : -20 °C - +40 °C / 1000 m									Locked rotor time (hot / cold) : 0 s 27.9 s								

Sound level (SPL / SWL) at 50Hz 60Hz	73 / 86 dB(A) ^{2) 3)}	77 / 90 dB(A) ^{2) 3)}	Vibration severity grade	A
Moment of inertia	0.2200 kg m²		Thermal class	F
Bearing DE NDE	6213 Z C3	6213 Z C3	Duty type	S1
bearing lifetime L _{10mh} F _{Rad,min} for coupling operation 50 60Hz ¹⁾	40000 h	32000 h	Direction of rotation	bidirectional
Regreasing device	Without		Frame material	cast iron
Grease nipple	-/-		Net weight of the motor (IM B3)	280 kg
Type of bearing	Locating bearing NDE		Coating (paint finish)	Standard paint finish C2
Condensate drainage holes	With (standard)		Color, paint shade	RAL7030
External earthing terminal	With (standard)		Motor protection	(A) without (Standard)
			Method of cooling	IC411 - self ventilated, surface cooled

Terminal box position	top	Max. cross-sectional area	35 mm²
Material of terminal box	cast iron	Cable diameter from ... to ...	27 mm - 35 mm
Type of terminal box	TB1 L01	Cable entry	2xM50x1,5
Contact screw thread	M8	Cable gland	2 plugs

I_R/I_N = locked rotor current / current nominal	1) L_{10th} according to DIN ISO 281 10/2010	3) Value is valid only for DOL operation with motor design IC411
M_R/M_N = locked rotor torque / torque nominal	2) at rated power / at full load	
M_R/M_N = break down torque / nominal torque		

Transmittal, reproduction, dissemination and/or editing of this document as well as utilization of its contents and communication thereof to others without express authorization are prohibited. Offenders will be held liable for payment of damages. All rights created by patent grant or registration of a utility model or design patent are reserved.

Responsible department IN LVM	Technical reference	Created by SPC	Approved by Created automatically	Technical data are subject to change! There may be discrepancies between calculated and rating plate values.		Link documents	
	Document type Technical data sheet			Document status Released			
	Document title 1LE1502-2BA23-4AA4			Document number TDS-240510-223521			
Restricted © Innomotics 2024				Revision AA	Creation date 2024-05-10	Language en	Page 1/1