



Figure similar

MLFB-Ordering data

1PH1133-1HD12-2GA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data		Mechanical data	
Rated power	11.0 kW	Motor type	Squirrel cage asynchronous motor
Rated speed	1000 rpm	Shaft height	132
Rated torque	105.0 Nm	Cooling	Forced-air cooling via fan
Rated current	28.3 A	Vibration severity grade	Grade B
Rated voltage	301 V	Degree of protection	IP54
Maximum speed	6000 rpm	Design acc. to Code I	IM B5 / IM V1
Maximum current	56.6 A	Color	Anthracite 614 / ~ RAL7016
Power for duty type S6-25%, maximum	16.50 kW	Shaft end	Feather key with half key balancing
Standstill torque for duty type S6-25%, maximum	158.0 Nm	Sound pressure level (1m)	72 dB
Standstill current for duty type S6-25%, maximum	40.0 A	Thermal class	F
Field weakening speed, max.	3000 rpm	Mounting type	Flange (round)
Supply voltage, max.	355 V	Encoder system	Absolute encoder single-turn (20 bit)
Line frequency	35.0 Hz		

Ambient conditions	
Ambient temperature	
Operation	-15 ... 40 °C
Storage	-20 ... 65 °C
Relative humidity	
Max. operation	90 %
Bearing, max.	95 %