



Figure similar

MLFB-Ordering data

1PH1133-1LF10-2GA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data		Mechanical data	
Rated power	15.0 kW	Motor type	Squirrel cage asynchronous motor
Rated speed	1500 rpm	Shaft height	132
Rated torque	95.5 Nm	Cooling	Forced-air cooling via fan
Rated current	36.7 A	Vibration severity grade	Grade B
Rated voltage	317 V	Degree of protection	IP54
Maximum speed	8000 rpm	Design acc. to Code I	IM B3 / IM V5
Maximum current	73.4 A	Color	Anthracite 614 / ~ RAL7016
Power for duty type S6-25%, maximum	22.50 kW	Shaft end	Feather key with half key balancing
Standstill torque for duty type S6-25%, maximum	143.0 Nm	Sound pressure level (1m)	72 dB
Standstill current for duty type S6-25%, maximum	52.0 A	Thermal class	F
Field weakening speed, max.	4000 rpm	Mounting type	Foot-mounted
Supply voltage, max.	355 V	Encoder system	Incremental encoder, TTL 2500 ppr (13 bit)
Line frequency	50.8 Hz		
Ambient conditions			

Ambient temperature	
Operation	-15 ... 40 °C
Storage	-20 ... 65 °C
Relative humidity	
Max. operation	90 %
Bearing, max.	95 %