



Figure similar

MLFB-Ordering data

1PH1105-1HF10-2GA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data		Mechanical data	
Rated power	7.5 kW	Motor type	Squirrel cage asynchronous motor
Rated speed	1500 rpm		
Rated torque	48.0 Nm	Shaft height	100
Rated current	19.6 A	Cooling	Forced-air cooling via fan
Rated voltage	327 V		
Maximum speed	10000 rpm	Vibration severity grade	Grade B
Maximum current	39.2 A	Degree of protection	IP54
Power for duty type S6-25%, maximum	11.25 kW	Design acc. to Code I	IM B3 / IM V5
		Color	Anthracite 614 / ~ RAL7016
		Shaft end	Feather key with half key balancing
Standstill torque for duty type S6-25%, maximum	72.0 Nm	Sound pressure level (1m)	72 dB
Standstill current for duty type S6-25%, maximum	28.0 A		
Field weakening speed, max.	4300 rpm	Thermal class	F
Supply voltage, max.	355 V	Mounting type	Foot-mounted
Line frequency	52.6 Hz	Encoder system	Absolute encoder single-turn (20 bit)
Ambient conditions			
Ambient temperature			
Operation	-15 ... 40 °C		
Storage	-20 ... 65 °C		
Relative humidity			
Max. operation	90 %		
Bearing, max.	95 %		