

Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data

1FK7040-2AK71-1RB2

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

| Engineering data | | Mechanical data | | | |
|---------------------------|-------------------------|-----------------------------|------------------------------------|------------------------|---|
| Rated speed (100 K) | 6000 rpm | Motor type | Permanent-magnet synchronous motor | | |
| Number of poles | 8 | Motor type | Compact | | |
| Rated torque (100 K) | 1.1 Nm | Shaft height | 48 | | |
| Rated current | 1.9 A | Cooling | Natural cooling | | |
| Static torque (60 K) | 1.30 Nm | Radial runout tolerance | 0.040 mm | | |
| Static torque (100 K) | 1.6 Nm | Concentricity tolerance | 0.08 mm | | |
| Stall current (60 K) | 1.90 A | Axial runout tolerance | 0.08 mm | | |
| Stall current (100 K) | 2.35 A | Vibration severity grade | Grade A | | |
| Moment of inertia | 1.920 kgcm ² | Connector size | 1 | | |
| Efficiency | 88.0 % | Degree of protection | IP65 and DE flange IP67 | | |
| Physical constants | | Design acc. to Code I | IM B5 (IM V1, IM V3) | | |
| | | Torque constant | 0.68 Nm/A | Temperature monitoring | Pt1000 temperature sensor |
| | | Voltage constant at 20° C | 43.4 V/1000*min ⁻¹ | Electrical connectors | Connectors for signals and power rotatable |
| | | Winding resistance at 20° C | 2.87 Ω | Color of the housing | Standard (Anthracite RAL 7016) |
| | | Rotating field inductance | 16.5 mH | Holding brake | with holding brake |
| | | Electrical time constant | 5.70 ms | Shaft extension | Feather key |
| | | Mechanical time constant | 3.00 ms | Encoder system | Encoder AM20DQI: absolute encoder 20 bits (resolution 1048576, encoder-internal 512 S/R) + 12 bits multi-turn (traversing range 4096 revolutions) |
| | | Thermal time constant | 25 min | | |
| | | Shaft torsional stiffness | 13000 Nm/rad | | |
| | | Net weight of the motor | 3.9 kg | | |



Figure similar

MLFB-Ordering data

1FK7040-2AK71-1RB2

Optimum operating point

| | |
|---------------|----------|
| Optimum speed | 6000 rpm |
| Optimum power | 0.7 kW |

Limiting data

| | |
|-----------------------------------|----------|
| Max. permissible speed (mech.) | 9000 rpm |
| Max. permissible speed (inverter) | 9000 rpm |
| Maximum torque | 5.1 Nm |
| Maximum current | 7.7 A |

Holding brake

| | |
|-----------------------|------------------------|
| Holding brake version | Permanent-magnet brake |
| Holding torque | 4.0 Nm |
| Power supply voltage | DC 24 V \pm 10 % |
| Coil current | 0.5 A |
| Opening time | 70 ms |
| Closing time | 30 ms |
| Highest braking work | 150 J |

Recommended Motor Module

| | |
|--------------------------|---------|
| Rated inverter current | 3 A |
| Maximum inverter current | 9 A |
| Maximum torque | 5.10 Nm |