



Figure similar

MLFB-Ordering data

1PH1131-1LD10-0GA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data		Mechanical data	
Rated power	7.5 kW	Motor type	Squirrel cage asynchronous motor
Rated speed	1000 rpm		
Rated torque	71.6 Nm	Shaft height	132
Rated current	26.6 A	Cooling	Forced-air cooling via fan
Rated voltage	220 V	Vibration severity grade	Grade B
Maximum speed	6000 rpm	Degree of protection	IP54
Maximum current	53.2 A	Design acc. to Code I	IM B3 / IM V5
Power for duty type S6-25%, maximum	11.25 kW	Color	Anthracite 614 / ~ RAL7016
Standstill torque for duty type S6-25%, maximum	107.0 Nm	Shaft end	Plain shaft
Standstill current for duty type S6-25%, maximum	38.0 A	Sound pressure level (1m)	72 dB
Field weakening speed, max.	5000 rpm	Thermal class	F
Supply voltage, max.	355 V	Mounting type	Foot-mounted
Line frequency	35.2 Hz	Encoder system	Incremental encoder, TTL 2500 ppr (13 bit)
Ambient conditions			

Ambient temperature	
Operation	-15 ... 40 °C
Storage	-20 ... 65 °C
Relative humidity	
Max. operation	90 %
Bearing, max.	95 %