



Figure similar

MLFB-Ordering data

1FK7081-2AH71-1UB1

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data		Mechanical data	
Rated speed (100 K)	4500 rpm	Motor type	Permanent-magnet synchronous motor
Number of poles	8	Motor type	Compact
Rated torque (100 K)	3.8 Nm	Shaft height	80
Rated current	4.9 A	Cooling	Natural cooling
Static torque (60 K)	10.00 Nm	Radial runout tolerance	0.050 mm
Static torque (100 K)	12.0 Nm	Concentricity tolerance	0.10 mm
Stall current (60 K)	10.60 A	Axial runout tolerance	0.10 mm
Stall current (100 K)	13.10 A	Vibration severity grade	Grade A
Moment of inertia	23.500 kgcm ²	Connector size	1
Efficiency	93.0 %	Degree of protection	IP65
Physical constants		Design acc. to Code I	IM B5 (IM V1, IM V3)
		Temperature monitoring	Pt1000 temperature sensor
Torque constant	0.92 Nm/A	Electrical connectors	Connectors for signals and power rotatable
Voltage constant at 20° C	59.0 V/1000*min ⁻¹	Color of the housing	Standard (Anthracite RAL 7016)
Winding resistance at 20° C	0.19 Ω	Holding brake	with holding brake
Rotating field inductance	3.4 mH	Shaft extension	Feather key
Electrical time constant	17.90 ms	Encoder system	Resolver R15DQ: resolver 15 bits (resolution 32768, internal multi-pole)
Mechanical time constant	1.36 ms		
Thermal time constant	45 min		
Shaft torsional stiffness	76000 Nm/rad		
Net weight of the motor	15.9 kg		



Figure similar

MLFB-Ordering data

1FK7081-2AH71-1UB1

Optimum operating point

Optimum speed	3000 rpm
Optimum power	2.8 kW

Limiting data

Max. permissible speed (mech.)	6000 rpm
Max. permissible speed (inverter)	6000 rpm
Maximum torque	37.0 Nm
Maximum current	45.0 A

Holding brake

Holding brake version	Permanent-magnet brake
Holding torque	22.0 Nm
Power supply voltage	DC 24 V \pm 10 %
Coil current	0.9 A
Opening time	200 ms
Closing time	60 ms
Highest braking work	1400 J

Recommended Motor Module

Rated inverter current	18 A
Maximum inverter current	54 A
Maximum torque	37.00 Nm