

## Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data

1FK7083-2AC71-1BA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

| Engineering data            |                                | Mechanical data          |   |
|-----------------------------|--------------------------------|--------------------------|---|
| Rated speed (100 K)         | 2000 rpm                       | Motor type               | Permanent-magnet synchronous motor                    |
| Number of poles             | 8                              | Motor type               | Compact   |
| Rated torque (100 K)        | 12.5 Nm                        | Shaft height             | 80  |
| Rated current               | 6.3 A                          | Cooling                  | Natural cooling                                       |
| Static torque (60 K)        | 13.30 Nm                       | Radial runout tolerance  | 0.050 mm  |
| Static torque (100 K)       | 16.0 Nm                        | Concentricity tolerance  | 0.10 mm   |
| Stall current (60 K)        | 6.10 A                         | Axial runout tolerance   | 0.10 mm   |
| Stall current (100 K)       | 7.50 A                         | Vibration severity grade | Grade A   |
| Moment of inertia           | 26.000 kgcm <sup>2</sup>       | Connector size           | 1   |
| Efficiency                  | 93.0 %                         | Degree of protection     | IP64  |
| Physical constants          |                                | Design acc. to Code I    | IM B5 (IM V1, IM V3)                                  |
| Torque constant             | 2.13 Nm/A                      | Temperature monitoring   | Pt1000 temperature sensor                             |
| Voltage constant at 20° C   | 138.5 V/1000*min <sup>-1</sup> | Electrical connectors    | Connectors for signals and power rotatable            |
| Winding resistance at 20° C | 0.66 Ω                         | Color of the housing     | Standard (Anthracite RAL 7016)                        |
| Rotating field inductance   | 12.8 mH                        | Holding brake            | without holding brake                                 |
| Electrical time constant    | 19.40 ms                       | Shaft extension          | Feather key   |
| Mechanical time constant    | 1.13 ms                        | Encoder system           | Encoder AS24DQI: absolute encoder single-turn 24 bits |
| Thermal time constant       | 50 min                         |                          |   |
| Shaft torsional stiffness   | 101000 Nm/rad                  |                          |   |
| Net weight of the motor     | 15.6 kg                        |                          |   |



Figure similar

MLFB-Ordering data

1FK7083-2AC71-1BA0

| Optimum operating point           |          | Recommended Motor Module |          |
|-----------------------------------|----------|--------------------------|----------|
| Optimum speed                     | 2000 rpm | Rated inverter current   | 9 A      |
| Optimum power                     | 2.6 kW   | Maximum inverter current | 27 A     |
| Limiting data                     |          | Maximum torque           | 49.30 Nm |
| Max. permissible speed (mech.)    | 6000 rpm |                          |          |
| Max. permissible speed (inverter) | 4150 rpm |                          |          |
| Maximum torque                    | 50.0 Nm  |                          |          |
| Maximum current                   | 27.5 A   |                          |          |