



Figure similar

Article No. : 1FK7083-2AH74-1TH1

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Engineering data

| | |
|-----------------------|--------------------------|
| Rated speed (100 K) | 4,500 rpm |
| Number of poles | 8 |
| Rated torque (100 K) | 3.0 Nm |
| Rated current | 3.6 A |
| Static torque (60 K) | 13.30 Nm |
| Static torque (100 K) | 16.00 Nm |
| Stall current (60 K) | 12.20 A |
| Stall current (100 K) | 15.00 A |
| Moment of inertia | 29.500 kgcm ² |
| Efficiency | 93.0 % |

Physical constants

| | |
|-----------------------------|-------------------------------|
| Torque constant | 1.06 Nm/A |
| Voltage constant at 20° C | 69.0 V/1000*min ⁻¹ |
| Winding resistance at 20° C | 0.17 Ω |
| Rotating field inductance | 3.2 mH |
| Electrical time constant | 19.30 ms |
| Mechanical time constant | 1.14 ms |
| Thermal time constant | 50 min |
| Shaft torsional stiffness | 72,000 Nm/rad |
| Net weight of the motor | 18.6 kg |

Mechanical data

| | |
|--------------------------|--------------------------------------------|
| Motor type | Permanent-magnet synchronous motor |
| Motor type | Compact |
| Shaft height | 80 |
| Cooling | Natural cooling |
| Radial runout tolerance | 0.050 mm |
| Concentricity tolerance | 0.10 mm |
| Axial runout tolerance | 0.10 mm |
| Vibration severity grade | Grade A |
| Connector size | 1 |
| Degree of protection | IP65 |
| Design acc. to Code I | IM B5 (IM V1, IM V3) |
| Temperature monitoring | Pt1000 temperature sensor |
| Electrical connectors | Connectors for signals and power rotatable |
| Color of the housing | Standard (Anthracite RAL 7016) |
| Holding brake | with holding brake |
| Shaft end | Plain shaft |
| Encoder system | Resolver 2-pole |

Optimum operating point

| | |
|---------------|-----------|
| Optimum speed | 3,000 rpm |
| Optimum power | 3.3 kW |

Limiting data

| | |
|-----------------------------------|-----------|
| Max. permissible speed (mech.) | 6,000 rpm |
| Max. permissible speed (inverter) | 6,000 rpm |
| Maximum torque | 50.0 Nm |
| Maximum current | 55.0 A |

Holding brake

| | |
|-----------------------|------------------------|
| Holding brake version | Permanent-magnet brake |
| Holding torque | 22.0 Nm |
| Power supply voltage | DC 24 V ± 10 % |
| Coil current | 0.9 A |
| Opening time | 200 ms |
| Closing time | 60 ms |
| Highest braking work | 1,400 J |

Recommended Motor Module

| | |
|--------------------------|----------|
| Rated inverter current | 18 A |
| Maximum inverter current | 54 A |
| Maximum torque | 49.30 Nm |