



Figure similar

MLFB-Ordering data

1FK7083-2AF71-1QB2

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data

Rated speed (100 K) 3000 rpm

Number of poles 8

Rated torque (100 K) 10.5 Nm

Rated current 7.2 A

Static torque (60 K) 13.30 Nm

Static torque (100 K) 16.00 Nm

Stall current (60 K) 8.20 A

Stall current (100 K) 10.10 A

Moment of inertia 29.500 kgcm²

Efficiency 93.0 %

Physical constants

Torque constant 1.58 Nm/A

Voltage constant at 20° C 102.5 V/1000*min⁻¹

Winding resistance at 20° C 0.38 Ω

Rotating field inductance 7.0 mH

Electrical time constant 18.60 ms

Mechanical time constant 1.18 ms

Thermal time constant 50 min

Shaft torsional stiffness 72000 Nm/rad

Net weight of the motor 18.6 kg

Mechanical data

Motor type Permanent-magnet synchronous motor

Motor type Compact

Shaft height 80

Cooling Natural cooling

Radial runout tolerance 0.050 mm

Concentricity tolerance 0.10 mm

Axial runout tolerance 0.10 mm

Vibration severity grade Grade A

Connector size 1

Degree of protection IP65 and DE flange IP67

Design acc. to Code I IM B5 (IM V1, IM V3)

Temperature monitoring Pt1000 temperature sensor

Electrical connectors Connectors for signals and power rotatable

Color of the housing Standard (Anthracite RAL 7016)

Holding brake with holding brake

Shaft end Feather key

Encoder system Encoder AS20DQI: absolute encoder single-turn 20 bits



Figure similar

MLFB-Ordering data

1FK7083-2AF71-1QB2

Optimum operating point

Optimum speed	3000 rpm
Optimum power	3.3 kW

Limiting data

Max. permissible speed (mech.)	6000 rpm
Max. permissible speed (inverter)	5600 rpm
Maximum torque	50.0 Nm
Maximum current	37.0 A

Holding brake

Holding brake version	Permanent-magnet brake
Holding torque	22.0 Nm
Power supply voltage	DC 24 V \pm 10 %
Coil current	0.9 A
Opening time	200 ms
Closing time	60 ms
Highest braking work	1400 J

Recommended Motor Module

Rated inverter current	9 A
Maximum inverter current	27 A
Maximum torque	40.00 Nm