

## Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data

1FK7100-2AC71-1QG1

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data		Mechanical data	
Rated speed (100 K)	2000 rpm	Motor type	Permanent-magnet synchronous motor
Number of poles	8	Motor type	Compact
Rated torque (100 K)	14.5 Nm	Shaft height	100
Rated current	7.1 A	Cooling	Natural cooling
Static torque (60 K)	14.90 Nm	Radial runout tolerance	0.050 mm
Static torque (100 K)	18.0 Nm	Concentricity tolerance	0.10 mm
Stall current (60 K)	6.80 A	Axial runout tolerance	0.10 mm
Stall current (100 K)	8.40 A	Vibration severity grade	Grade A
Moment of inertia	54.000 kgcm <sup>2</sup>	Connector size	1
Efficiency	92.0 %	Degree of protection	IP65
<b>Physical constants</b>		Design acc. to Code I	IM B5 (IM V1, IM V3)
		Temperature monitoring	Pt1000 temperature sensor
Torque constant	2.14 Nm/A	Electrical connectors	Connectors for signals and power rotatable
Voltage constant at 20° C	138.0 V/1000*min <sup>-1</sup>	Color of the housing	Standard (Anthracite RAL 7016)
Winding resistance at 20° C	0.55 Ω	Holding brake	without holding brake
Rotating field inductance	12.7 mH	Shaft extension	Plain shaft
Electrical time constant	23.00 ms	Encoder system	Encoder AS20DQI: absolute encoder single-turn 20 bits
Mechanical time constant	1.95 ms		
Thermal time constant	55 min		
Shaft torsional stiffness	183000 Nm/rad		
Net weight of the motor	17.6 kg		



Figure similar

MLFB-Ordering data

1FK7100-2AC71-1QG1

Optimum operating point		Recommended Motor Module	
Optimum speed	2000 rpm	Rated inverter current	9 A
Optimum power	3.0 kW	Maximum inverter current	27 A
Limiting data		Maximum torque	53.40 Nm
Max. permissible speed (mech.)	5000 rpm		
Max. permissible speed (inverter)	4200 rpm		
Maximum torque	55.0 Nm		
Maximum current	28.0 A		