

Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data

1FK7103-2AF74-1SH1

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data		Mechanical data			
Rated speed (100 K)	3000 rpm	Motor type	Permanent-magnet synchronous motor		
Number of poles	8	Motor type	Compact		
Rated torque (100 K)	14.0 Nm	Shaft height	100		
Rated current	11.5 A	Cooling	Natural cooling		
Static torque (60 K)	30.00 Nm	Radial runout tolerance	0.050 mm		
Static torque (100 K)	36.0 Nm	Concentricity tolerance	0.10 mm		
Stall current (60 K)	21.00 A	Axial runout tolerance	0.10 mm		
Stall current (100 K)	26.00 A	Vibration severity grade	Grade A		
Moment of inertia	112.000 kgcm ²	Connector size	1.5		
Efficiency	93.0 %	Degree of protection	IP65		
Physical constants		Design acc. to Code I	IM B5 (IM V1, IM V3)		
		Temperature monitoring	Pt1000 temperature sensor		
		Electrical connectors	Connectors for signals and power rotatable		
		Color of the housing	Standard (Anthracite RAL 7016)		
		Holding brake	with holding brake		
		Shaft extension	Plain shaft		
		Encoder system	Multi-pole resolver (number of pole pairs corresponds to number of pole pairs of the motor)		
		Torque constant	1.39 Nm/A		
		Voltage constant at 20° C	89.5 V/1000*min ⁻¹		
		Winding resistance at 20° C	0.09 Ω		
Rotating field inductance	2.4 mH				
Electrical time constant	27.00 ms				
Mechanical time constant	1.46 ms				
Thermal time constant	65 min				
Shaft torsional stiffness	108000 Nm/rad				
Net weight of the motor	33.0 kg				



Figure similar

MLFB-Ordering data

1FK7103-2AF74-1SH1

Optimum operating point

Optimum speed	2500 rpm
Optimum power	5.4 kW

Limiting data

Max. permissible speed (mech.)	5000 rpm
Max. permissible speed (inverter)	5000 rpm
Maximum torque	108.0 Nm
Maximum current	84.0 A

Holding brake

Holding brake version	Permanent-magnet brake
Holding torque	43.0 Nm
Power supply voltage	DC 24 V \pm 10 %
Coil current	1.0 A
Opening time	300 ms
Closing time	70 ms
Highest braking work	3380 J

Recommended Motor Module

Rated inverter current	30 A
Maximum inverter current	90 A
Maximum torque	108.00 Nm