

Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data

1FK7080-2AF71-1PH2

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data		Mechanical data																					
Rated speed (100 K)	3000 rpm	Motor type	Permanent-magnet synchronous motor																				
Number of poles	8	Motor type	Compact																				
Rated torque (100 K)	6.8 Nm	Shaft height	80																				
Rated current	4.4 A	Cooling	Natural cooling																				
Static torque (60 K)	6.60 Nm	Radial runout tolerance	0.050 mm																				
Static torque (100 K)	8.00 Nm	Concentricity tolerance	0.10 mm																				
Stall current (60 K)	4.00 A	Axial runout tolerance	0.10 mm																				
Stall current (100 K)	4.90 A	Vibration severity grade	Grade A																				
Moment of inertia	17.500 kgcm ²	Connector size	1																				
Efficiency	92.0 %	Degree of protection	IP65 and DE flange IP67																				
<table border="1"> <thead> <tr> <th colspan="2">Physical constants</th> </tr> </thead> <tbody> <tr> <td>Torque constant</td> <td>1.61 Nm/A</td> </tr> <tr> <td>Voltage constant at 20° C</td> <td>105.0 V/1000*min⁻¹</td> </tr> <tr> <td>Winding resistance at 20° C</td> <td>0.98 Ω</td> </tr> <tr> <td>Rotating field inductance</td> <td>17.2 mH</td> </tr> <tr> <td>Electrical time constant</td> <td>17.50 ms</td> </tr> <tr> <td>Mechanical time constant</td> <td>1.52 ms</td> </tr> <tr> <td>Thermal time constant</td> <td>40 min</td> </tr> <tr> <td>Shaft torsional stiffness</td> <td>81000 Nm/rad</td> </tr> <tr> <td>Net weight of the motor</td> <td>13.3 kg</td> </tr> </tbody> </table>		Physical constants		Torque constant	1.61 Nm/A	Voltage constant at 20° C	105.0 V/1000*min ⁻¹	Winding resistance at 20° C	0.98 Ω	Rotating field inductance	17.2 mH	Electrical time constant	17.50 ms	Mechanical time constant	1.52 ms	Thermal time constant	40 min	Shaft torsional stiffness	81000 Nm/rad	Net weight of the motor	13.3 kg	Design acc. to Code I	IM B5 (IM V1, IM V3)
		Physical constants																					
		Torque constant	1.61 Nm/A																				
		Voltage constant at 20° C	105.0 V/1000*min ⁻¹																				
		Winding resistance at 20° C	0.98 Ω																				
		Rotating field inductance	17.2 mH																				
		Electrical time constant	17.50 ms																				
		Mechanical time constant	1.52 ms																				
		Thermal time constant	40 min																				
		Shaft torsional stiffness	81000 Nm/rad																				
Net weight of the motor	13.3 kg																						
Temperature monitoring	Pt1000 temperature sensor	Electrical connectors	Connectors for signals and power rotatable																				
Color of the housing	Standard (Anthracite RAL 7016)	Holding brake	with holding brake																				
Shaft end	Plain shaft	Encoder system	Resolver R14DQ: resolver 14 bits (resolution 16384, internal 2-pole)																				



Figure similar

MLFB-Ordering data

1FK7080-2AF71-1PH2

Optimum operating point

Optimum speed	3000 rpm
Optimum power	2.1 kW

Limiting data

Max. permissible speed (mech.)	6000 rpm
Max. permissible speed (inverter)	5500 rpm
Maximum torque	25.0 Nm
Maximum current	18.0 A

Holding brake

Holding brake version	Permanent-magnet brake
Holding torque	22.0 Nm
Power supply voltage	DC 24 V \pm 10 %
Coil current	0.9 A
Opening time	200 ms
Closing time	60 ms
Highest braking work	1400 J

Recommended Motor Module

Rated inverter current	5 A
Maximum inverter current	15 A
Maximum torque	22.10 Nm