

Data sheet for SIMOTICS S-1FK7

MLFB-Ordering data

1FK7080-2AH71-1CA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data		Mechanical data			
Rated speed (100 K)	4500 rpm	Motor type	Permanent-magnet synchronous motor		
Number of poles	8	Motor type	Compact		
Rated torque (100 K)	4.5 Nm	Shaft height	80		
Rated current	4.8 A	Cooling	Natural cooling		
Static torque (60 K)	6.60 Nm	Radial runout tolerance	0.050 mm		
Static torque (100 K)	8.00 Nm	Concentricity tolerance	0.10 mm		
Stall current (60 K)	6.00 A	Axial runout tolerance	0.10 mm		
Stall current (100 K)	7.40 A	Vibration severity grade	Grade A		
Moment of inertia	14.200 kgcm ²	Connector size	1		
Efficiency	92.0 %	Degree of protection	IP64		
<th colspan="2">Physical constants</th>		Physical constants		Design acc. to Code I	IM B5 (IM V1, IM V3)
		Torque constant	1.08 Nm/A	Temperature monitoring	Pt1000 temperature sensor
		Voltage constant at 20° C	68.5 V/1000*min ⁻¹	Electrical connectors	Connectors for signals and power rotatable
		Winding resistance at 20° C	0.42 Ω	Color of the housing	Standard (Anthracite RAL 7016)
		Rotating field inductance	7.3 mH	Holding brake	without holding brake
		Electrical time constant	17.30 ms	Shaft end	Feather key
		Mechanical time constant	1.54 ms	Encoder system	Encoder AM24DQI: absolute encoder 24 bits (resolution 16777216, encoder-internal 2048 S/R) + 12 bits multi-turn (traversing range 4096 revolutions)
		Thermal time constant	40 min		
		Shaft torsional stiffness	120000 Nm/rad		
		Net weight of the motor	10.3 kg		



Figure similar

MLFB-Ordering data

1FK7080-2AH71-1CA0

Optimum operating point

Optimum speed 4000 rpm

Optimum power 2.4 kW

Limiting data

Max. permissible speed (mech.) 6000 rpm

Max. permissible speed (inverter) 6000 rpm

Maximum torque 25.0 Nm

Maximum current 27.5 A

Recommended Motor Module

Rated inverter current 9 A

Maximum inverter current 27 A

Maximum torque 24.70 Nm