

Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data

1FK7083-2AF71-1CH0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

| Engineering data | | Mechanical data | | | |
|---|--------------------------|-----------------------------|------------------------------------|------------------------|---|
| Rated speed (100 K) | 3000 rpm | Motor type | Permanent-magnet synchronous motor | | |
| Number of poles | 8 | Motor type | Compact | | |
| Rated torque (100 K) | 10.5 Nm | Shaft height | 80 | | |
| Rated current | 7.2 A | Cooling | Natural cooling | | |
| Static torque (60 K) | 13.30 Nm | Radial runout tolerance | 0.050 mm | | |
| Static torque (100 K) | 16.0 Nm | Concentricity tolerance | 0.10 mm | | |
| Stall current (60 K) | 8.20 A | Axial runout tolerance | 0.10 mm | | |
| Stall current (100 K) | 10.10 A | Vibration severity grade | Grade A | | |
| Moment of inertia | 29.500 kgcm ² | Connector size | 1 | | |
| Efficiency | 93.0 % | Degree of protection | IP64 | | |
| <th colspan="2">Physical constants</th> | | Physical constants | | Design acc. to Code I | IM B5 (IM V1, IM V3) |
| | | Torque constant | 1.58 Nm/A | Temperature monitoring | Pt1000 temperature sensor |
| | | Voltage constant at 20° C | 102.5 V/1000*min ⁻¹ | Electrical connectors | Connectors for signals and power rotatable |
| | | Winding resistance at 20° C | 0.38 Ω | Color of the housing | Standard (Anthracite RAL 7016) |
| | | Rotating field inductance | 7.0 mH | Holding brake | with holding brake |
| | | Electrical time constant | 18.60 ms | Shaft extension | Plain shaft |
| | | Mechanical time constant | 1.18 ms | Encoder system | Encoder AM24DQI: absolute encoder 24 bits (resolution 16777216, encoder-internal 2048 S/R) + 12 bits multi-turn (traversing range 4096 revolutions) |
| | | Thermal time constant | 50 min | | |
| | | Shaft torsional stiffness | 72000 Nm/rad | | |
| | | Net weight of the motor | 18.6 kg | | |



Figure similar

MLFB-Ordering data

1FK7083-2AF71-1CH0

Optimum operating point

| | |
|---------------|----------|
| Optimum speed | 3000 rpm |
| Optimum power | 3.3 kW |

Limiting data

| | |
|-----------------------------------|----------|
| Max. permissible speed (mech.) | 6000 rpm |
| Max. permissible speed (inverter) | 5600 rpm |
| Maximum torque | 50.0 Nm |
| Maximum current | 37.0 A |

Holding brake

| | |
|-----------------------|------------------------|
| Holding brake version | Permanent-magnet brake |
| Holding torque | 22.0 Nm |
| Power supply voltage | DC 24 V \pm 10 % |
| Coil current | 0.9 A |
| Opening time | 200 ms |
| Closing time | 60 ms |
| Highest braking work | 1400 J |

Recommended Motor Module

| | |
|--------------------------|----------|
| Rated inverter current | 9 A |
| Maximum inverter current | 27 A |
| Maximum torque | 40.00 Nm |