



Figure similar

MLFB-Ordering data

1FK7083-5AF71-1DG5

Client order no. :
 Order no. :
 Offer no. :
 Remarks :

Item no. :
 Consignment no. :
 Project :

Engineering data

Mechanical data

Rated speed (100 K)	3000 rpm
Number of poles	8
Rated torque (100 K)	10.5 Nm
Rated current	7.4 A
Static torque (60 K)	13.30 Nm
Static torque (100 K)	16.00 Nm
Stall current (60 K)	8.60 A
Stall current (100 K)	10.40 A
Moment of inertia	27.300 kgcm ²
Efficiency	93.0 %

Motor type	Permanent-magnet synchronous motor
Motor type	Compact
Shaft height	80
Cooling	Natural cooling
Radial runout tolerance	0.050 mm
Concentricity tolerance	0.10 mm
Axial runout tolerance	0.10 mm
Vibration severity grade	Grade A
Connector size	1
Degree of protection	IP65 and DE flange IP67
Design acc. to Code I	IM B5 (IM V1, IM V3)
Temperature monitoring	KTY84 temperature sensor in the stator winding
Electrical connectors	Connectors for signals and power rotatable
Color of the housing	Standard (Anthracite RAL 7016)
Holding brake	without holding brake
Shaft end	Plain shaft
Encoder system	Encoder IC22DQ: incremental encoder 22 bits (resolution 4194304, encoder-internal 2048 S/R) + commutation position 11 bits

Physical constants

Torque constant	1.52 Nm/A
Voltage constant at 20° C	97.0 V/1000*min ⁻¹
Winding resistance at 20° C	0.40 Ω
Rotating field inductance	6.0 mH
Electrical time constant	15.50 ms
Mechanical time constant	1.41 ms
Thermal time constant	50 min
Shaft torsional stiffness	105000 Nm/rad
Net weight of the motor	14.0 kg

MLFB-Ordering data

1FK7083-5AF71-1DG5

Figure similar

Optimum operating point

Optimum speed 3000 rpm

Optimum power 3.3 kW

Limiting data

Max. permissible speed (mech.) 6000 rpm

Max. permissible speed (inverter) 5900 rpm

Maximum torque 50.0 Nm

Maximum current 37.0 A

Recommended Motor Module

Rated inverter current 9 A

Maximum inverter current 18 A

Maximum torque 27.80 Nm