

Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1AV2073B

SIMOTICS GP - 71 M - IM B14 - 4p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	Project
Remarks		

Electrical data

Safe Area

U [V]	Δ / Y	f [Hz]	P [kW]	P [hp]	I [A]	n [1/min]	M [Nm]	η ³⁾			$\cos\phi$ ³⁾			I_A/I_N I_i/I_N	M_A/M_N T_i/T_N	M_K/M_N T_B/T_N	IE-CL
								4/4	3/4	2/4	4/4	3/4	2/4				
DOL duty (S1) - 155(F) to 130(B)																	
230	Δ	50	0.37	-/-	1.77	1380	2.5	72.7	73.2	69.9	0.72	0.63	0.49	4.0	2.5	2.5	IE2
400	Y	50	0.37	-/-	1.02	1380	2.5	72.7	73.2	69.9	0.72	0.63	0.49	4.0	2.5	2.5	IE2
460	Y	60	0.43	-/-	1.04	1680	2.5	72.0	72.4	69.4	0.72	0.63	0.50	4.5	2.6	2.7	IE2
460	Y	60	0.37	-/-	0.96	1705	2.0	72.0	71.2	66.9	0.67	0.58	0.45	5.0	3.0	3.2	IE2
IM B14 / IM 3601		FS 71 M		IP55		IEC/EN 60034		IEC, DIN, ISO, VDE, EN									
Environmental conditions : -20 °C - +40 °C / 1,000 m										Locked rotor time (hot / cold) : 38.4 s 49.1 s							

Mechanical data

Sound level (SPL / SWL) at 50Hz 60Hz	44 / 55 dB(A) ²⁾	47 / 58 dB(A) ²⁾	Vibration severity grade	A
Moment of inertia	0.0009 kg m ²		Thermal class	F
Bearing DE NDE	6202 2Z C3	6202 2Z C3	Duty type	S1
bearing lifetime			Direction of rotation	bidirectional
L_{10mh} , F_{Rad} min 50 60Hz Lubricants	40000 h	32000 h	Frame material	aluminum
Regreasing device	Unirex N3		Net weight of the motor (IM B3)	7 kg
Grease nipple	No		Coating (paint finish)	Standard paint finish C2
Type of bearing	Preloaded bearing DE		Color, paint shade	RAL7030
Condensate drainage holes	No		Motor protection	(A) without (Standard)
External earthing terminal	No		Method of cooling	IC411 - self ventilated, surface cooled

Terminal box

Terminal box position	top	Max. cross-sectional area	1.5 mm ²
Material of terminal box	Aluminium	Cable diameter from ... to ...	9 mm - 17 mm
Type of terminal box	TB1 B00	Cable entry	1xM25x1,5
Contact screw thread	M4	Cable gland	1 plug

Notes:

I_A/I_N = locked rotor current / current nominal
 M_A/M_N = locked rotor torque / torque nominal
 M_K/M_N = break down torque / nominal torque
 1) L10mh according to DIN ISO 281 10/2010
 2) at rated power / at full load
 3) Value is valid only for DOL operation with motor design IC411

responsible dep. DI MC LVM	technical reference	created by DT Configurator	approved by	<i>Technical data are subject to change! There may be discrepancies between calculated and rating plate values.</i>	Link documents
	document type datasheet	document status released			
	title 1LE1001-0CB32-2KA4	document number			
© Siemens AG 2021	rev. 01	creation date 2021-11-29	language en		