

Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1AV1162C

SIMOTICS GP - 160 M - IM B3 - 6p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	project

Remarks

Electrical data

Safe Area

U [V]	Δ / Y	f [Hz]	P [kW]	P [hp]	I [A]	n [1/min]	M [Nm]	η ³⁾			$\cos\phi$ ³⁾			I_A/I_N I_i/I_N	M_A/M_N T_i/T_N	M_K/M_N T_B/T_N	IE-CL
								4/4	3/4	2/4	4/4	3/4	2/4				
400	Δ	50	7.50	-/-	17.50	970	74.0	84.7	84.8	83.2	0.73	0.66	0.54	5.5	2.1	2.9	IE1
690	Y	50	7.50	-/-	10.10	970	74.0	84.7	84.8	83.2	0.73	0.66	0.54	5.5	2.1	2.9	IE1
460	Δ	60	8.60	-/-	16.70	1170	70.0	86.0	86.0	84.5	0.75	0.68	0.57	5.9	2.2	2.9	IE1

IM B3 / IM 1001	FS 160 M	72 kg	IP55	IEC/EN 60034	IEC, DIN, ISO, VDE, EN
-----------------	----------	-------	------	--------------	------------------------

Environmental conditions : -20 °C - +40 °C / 1,000 m

Mechanical data

Sound level (SPL / SWL) at 50Hz 60Hz	67.0 / 79.0 dB(A) ²⁾	70.0 / 82.0 dB(A) ²⁾	External earthing terminal	No
Moment of inertia	0.0560 kg m ²		Vibration severity grade	A
Bearing DE NDE	6209 2Z C3	6209 2Z C3	Insulation	155(F) to 130(B)
bearing lifetime			Duty type	S1
L _{10mh} F _{Rad min} for coupling operation 50 60Hz ¹⁾	40000 h	32000 h	Direction of rotation	bidirectional
Lubricants	Unirex N3		Frame material	aluminum
Regreasing device	No		Coating (paint finish)	Standard paint finish C2
Grease nipple	-/-		Color, paint shade	RAL7030
Type of bearing	Locating bearing NDE		Motor protection	(A) without (Standard)
Condensate drainage holes	No		Method of cooling	IC411 - self ventilated, surface cooled

Terminal box


Terminal box position	top	Max. cross-sectional area	16.0 mm ²
Material of terminal box	Aluminium	Cable diameter from ... to ...	19.0 mm - 28.0 mm
Type of terminal box	TB1 J00	Cable entry	2xM40x1,5
Contact screw thread	M5	Cable gland	2 plugs

Notes:

I_A/I_N = locked rotor current / current nominal
 M_A/M_N = locked rotor torque / torque nominal
 M_K/M_N = break down torque / nominal torque

1) L10mh according to DIN ISO 281 10/2010
 2) at rated power / at full load

3) Value is valid only for DOL operation with motor design IC411

responsible dep. DI MC LVM	technical reference	created by DT Configurator	approved by	Technical data are subject to change! There may be discrepancies between calculated and rating plate values.	
	document type datasheet	document status released		customer	
	title 1LE1002-1DC23-4AA4	document number			
© Siemens AG 2021	rev. 01	creation date 2021-01-17 19:52	language en	Page 1/1	