

## Data sheet for SIMOTICS S-1FK7

MLFB-Ordering data

1FK7084-2AF74-1SA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data		Mechanical data	
Rated speed (100 K)	3000 rpm	Motor type	Permanent-magnet synchronous motor
Number of poles	8	Motor type	Compact
Rated torque (100 K)	10.0 Nm	Shaft height	80
Rated current	6.5 A	Cooling	Natural cooling
Static torque (60 K)	16.60 Nm	Radial runout tolerance	0.050 mm
Static torque (100 K)	20.00 Nm	Concentricity tolerance	0.10 mm
Stall current (60 K)	9.80 A	Axial runout tolerance	0.10 mm
Stall current (100 K)	12.10 A	Vibration severity grade	Grade A
Moment of inertia	32.500 kgcm <sup>2</sup>	Connector size	1
Efficiency	93.0 %	Degree of protection	IP64
<b>Physical constants</b>		Design acc. to Code I	IM B5 (IM V1, IM V3)
		Temperature monitoring	Pt1000 temperature sensor
Torque constant	1.66 Nm/A	Electrical connectors	Connectors for signals and power rotatable
Voltage constant at 20° C	106.5 V/1000*min <sup>-1</sup>	Color of the housing	Standard (Anthracite RAL 7016)
Winding resistance at 20° C	0.28 Ω	Holding brake	without holding brake
Rotating field inductance	5.9 mH	Shaft end	Feather key
Electrical time constant	21.00 ms	Encoder system	Multi-pole resolver (number of pole pairs corresponds to number of pole pairs of the motor)
Mechanical time constant	1.01 ms		
Thermal time constant	55 min		
Shaft torsional stiffness	93000 Nm/rad		
Net weight of the motor	18.3 kg		



Figure similar

MLFB-Ordering data

1FK7084-2AF74-1SA0

Optimum operating point		Recommended Motor Module	
Optimum speed	2500 rpm	Rated inverter current	18 A
Optimum power	3.2 kW	Maximum inverter current	54 A
Limiting data		Maximum torque	61.00 Nm
Max. permissible speed (mech.)	6000 rpm		
Max. permissible speed (inverter)	5400 rpm		
Maximum torque	61.0 Nm		
Maximum current	41.0 A		