

# Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1AV1164C

SIMOTICS GP - 160 L - IM B5 - 6p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	project

Remarks

## Electrical data

## Safe Area

U [V]	$\Delta / Y$	f [Hz]	P [kW]	P [hp]	I [A]	n [1/min]	M [Nm]	$\eta$ <sup>3)</sup>			$\cos\phi$ <sup>3)</sup>			$I_A/I_N$ $I_i/I_N$	$M_A/M_N$ $T_i/T_N$	$M_K/M_N$ $T_B/T_N$	IE-CL
								4/4	3/4	2/4	4/4	3/4	2/4				
400	$\Delta$	50	11.00	-/-	24.00	965	109.0	86.4	86.8	85.9	0.77	0.71	0.59	5.9	1.9	2.7	IE1
690	Y	50	11.00	-/-	13.80	965	109.0	86.4	86.8	85.9	0.77	0.71	0.59	5.9	1.9	2.7	IE1
460	$\Delta$	60	12.60	-/-	23.00	1165	103.0	89.0	89.3	88.3	0.77	0.71	0.61	6.3	1.9	2.7	IE1

IM B5 / IM 3001 FS 160 L 92 kg IP55 IEC/EN 60034 IEC, DIN, ISO, VDE, EN  
 Environmental conditions : -20 °C - +40 °C / 1,000 m

## Mechanical data

Sound level (SPL / SWL) at 50Hz 60Hz	67.0 / 79.0 dB(A) <sup>2)</sup>	70.0 / 82.0 dB(A) <sup>2)</sup>	External earthing terminal	No
Moment of inertia	0.0780 kg m <sup>2</sup>		Vibration severity grade	A
Bearing DE   NDE	6209 2Z C3	6209 2Z C3	Insulation	155(F) to 130(B)
<b>bearing lifetime</b>			Duty type	S1
L <sub>10mh</sub> F <sub>Rad min</sub> for coupling operation 50 60Hz <sup>1)</sup>	40000 h	32000 h	Direction of rotation	bidirectional
Lubricants	Unirex N3		Frame material	aluminum
Regreasing device	No		Coating (paint finish)	Standard paint finish C2
Grease nipple	-/-		Color, paint shade	RAL7030
Type of bearing	Locating bearing NDE		Motor protection	(A) without (Standard)
Condensate drainage holes	No		Method of cooling	IC411 - self ventilated, surface cooled

## Terminal box

Terminal box position	top	Max. cross-sectional area	16.0 mm <sup>2</sup>
Material of terminal box	Aluminium	Cable diameter from ... to ...	19.0 mm - 28.0 mm
Type of terminal box	TB1 J00	Cable entry	2xM40x1,5
Contact screw thread	M5	Cable gland	2 plugs

**Notes:**  
 $I_A/I_N$  = locked rotor current / current nominal  
 $M_A/M_N$  = locked rotor torque / torque nominal  
 $M_K/M_N$  = break down torque / nominal torque  
 1) L10mh according to DIN ISO 281 10/2010  
 2) at rated power / at full load  
 3) Value is valid only for DOL operation with motor design IC411

responsible dep. DI MC LVM	technical reference	created by DT Configurator	approved by	<i>Technical data are subject to change! There may be discrepancies between calculated and rating plate values.</i>			
<b>SIEMENS</b>	document type datasheet	document status released		customer			
	title 1LE1002-1DC43-4FA4	document number					
© Siemens AG 2021	rev. 01	creation date 2021-01-17 20:17	language en	Page 1/1			