

# Data sheet for three-phase Squirrel-Cage-Motors INNOMOTICS



Motor type : 1AV3083A

INNOMOTICS GP - 80 M - IM B5 - 2p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	Project

Remarks

Safe Area

## Electrical data

-/-

U [V]	$\Delta$ / Y	f [Hz]	P [kW]	P [hp]	I [A]	n [1/min]	M [Nm]	$\eta$ <sup>3)</sup>			$\cos\phi$ <sup>3)</sup>			$I_A/I_N$ $I_f/I_N$	$M_A/M_N$ $T_f/T_N$	$M_K/M_N$ $T_B/T_N$	IE-CL
								4/4	3/4	2/4	4/4	3/4	2/4				
<b>DOL duty (S1) - 155(F) to 130(B)</b>																	
230	$\Delta$	50	1.10	-/-	3.95	2885	3.6	82.7	83.9	83.1	0.85	0.80	0.69	7.1	3.0	3.3	IE3
400	Y	50	1.10	-/-	2.25	2885	3.6	82.7	83.9	83.1	0.85	0.80	0.69	7.1	3.0	3.3	IE3
460	Y	60	1.27	-/-	2.25	3480	3.5	84.0	84.6	83.4	0.85	0.80	0.71	7.4	2.8	3.4	IE3
460	Y	60	1.10	-/-	1.98	3500	3.0	84.0	84.0	82.0	0.83	0.77	0.67	8.4	3.3	4.0	IE3
IM B5 / IM 3001		FS 80 M		IP55		UKCA		IEC/EN 60034		IEC, DIN, ISO, VDE, EN							
Environmental conditions : -20 °C - +40 °C / 1000 m										Locked rotor time (hot / cold) : 14.4 s   19.5 s							

## Mechanical data

Sound level (SPL / SWL) at 50Hz 60Hz	60 / 71 dB(A) <sup>2) 3)</sup>	64 / 75 dB(A) <sup>2) 3)</sup>	Vibration severity grade	A
Moment of inertia	0.0013 kg m <sup>2</sup>		Thermal class	F
Bearing DE   NDE	6004 2Z C3	6004 2Z C3	Duty type	S1
<b>bearing lifetime</b>			Direction of rotation	bidirectional
$L_{10mh}$ $F_{Rad, min}$ for coupling operation 50 60Hz <sup>1)</sup>	40000 h	32000 h	Frame material	aluminum
Regreasing device	Without		Net weight of the motor (IM B3)	12 kg
Grease nipple	-/-		Coating (paint finish)	Standard paint finish C2
Type of bearing	Preloaded bearing DE		Color, paint shade	RAL7030
Condensate drainage holes	Without		Motor protection	(B) 1 PTC thermistor - for tripping (2 terminals)
External earthing terminal	Without		Method of cooling	IC411 - self ventilated, surface cooled

## Terminal box

Terminal box position	top	Max. cross-sectional area	1.5 mm <sup>2</sup>
Material of terminal box	Aluminium	Cable diameter from ... to ...	9 mm - 17 mm
Type of terminal box	TB1 E00	Cable entry	1xM25x1,5-1xM16x1,5
Contact screw thread	M4	Cable gland	2 plugs

$I_A/I_N$  = locked rotor current / current nominal  
 $M_A/M_N$  = locked rotor torque / torque nominal  
 $M_K/M_N$  = break down torque / nominal torque  
 1)  $L_{10mh}$  according to DIN ISO 281 10/2010  
 2) at rated power / at full load  
 3) Value is valid only for DOL operation with motor design IC411

Transmittal, reproduction, dissemination and/or editing of this document as well as utilization of its contents and communication thereof to others without express authorization are prohibited. Offenders will be held liable for payment of damages. All rights created by patent grant or registration of a utility model or design patent are reserved.

Responsible department IN LVM	Technical reference	Created by SPC	Approved by Created automatically	<i>Technical data are subject to change! There may be discrepancies between calculated and rating plate values.</i>	<a href="#">Link documents</a>	
<b>INNOMOTICS</b>	Document type Technical data sheet	Document status Released				
	Document title 1LE1003-ODA32-2FB4	Document number TDS-241111-134607				
Restricted	Revision AA	Creation date 2024-11-11	Language en			Page 1/1
© Innomotics 2024						