

Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1CV3252C

SIMOTICS SD - 250 M - IM B3 - 6p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	Project
Remarks		

Electrical data

Safe Area

U [V]	Δ / Y	f [Hz]	P [kW]	P [hp]	I [A]	n [1/min]	M [Nm]	η ³⁾			$\cos\phi$ ³⁾			I_A/I_N I_f/I_N	M_A/M_N T_f/T_N	M_K/M_N T_B/T_N	IE-CL
								4/4	3/4	2/4	4/4	3/4	2/4				
DOL duty (S1) - 155(F) to 130(B)																	
400	Δ	50	37.00	-/-	67.00	985	360.0	93.3	94.0	94.0	0.85	0.82	0.74	7.0	2.7	2.9	IE3
690	Y	50	37.00	-/-	39.00	985	360.0	93.3	94.0	94.0	0.85	0.82	0.74	7.0	2.7	2.9	IE3
IM B3 / IM 1001			FS 250 M		IP55		IEC/EN 60034		IEC, DIN, ISO, VDE, EN								

Environmental conditions : -20 °C - +40 °C / 1,000 m

Mechanical data

Sound level (SPL / SWL) at 50Hz 60Hz	62 / 75 dB(A) ²⁾	63 / 76 dB(A) ²⁾	Vibration severity grade	A
Moment of inertia	1.0000 kg m ²		Thermal class	F
Bearing DE NDE	6215 Z C3	6215 Z C3	Duty type	S1
bearing lifetime			Direction of rotation	bidirectional
L_{10mh} , F_{Rad} , m_{min} 50 60Hz Lubricants	40000 h	32000 h	Frame material	cast iron
Regreasing device	Unirex N3		Net weight of the motor (IM B3)	405 kg
Grease nipple	No		Coating (paint finish)	Standard paint finish C2
Type of bearing	Locating bearing NDE		Color, paint shade	RAL7030
Condensate drainage holes	Yes (standard)		Motor protection	(A) without (Standard)
External earthing terminal	Yes (standard)		Method of cooling	IC411 - self ventilated, surface cooled

Terminal box

Terminal box position	top	Max. cross-sectional area	120 mm ²
Material of terminal box	cast iron	Cable diameter from ... to ...	34 mm - 42 mm
Type of terminal box	TB1 N01	Cable entry	2xM63x1,5
Contact screw thread	M10	Cable gland	2 plugs

Notes:

I_A/I_N = locked rotor current / current nominal
 M_A/M_N = locked rotor torque / torque nominal
 M_K/M_N = break down torque / nominal torque
 1) L10mh according to DIN ISO 281 10/2010
 2) at rated power / at full load
 3) Value is valid only for DOL operation with motor design IC411

responsible dep. DI MC LVM	technical reference	created by DT Configurator	approved by	<i>Technical data are subject to change! There may be discrepancies between calculated and rating plate values.</i>	Link documents
	document type datasheet	document status released			document number
	title 1LE1503-2CC23-4AA4	rev. 01	creation date 2021-11-28		
© Siemens AG 2021					