

## Data sheet for SIMOTICS S-1FL6



Figure similar

MLFB-Ordering data

1FL6092-1AC61-2AB1

Client order no. :

Item no. :

Order no. :

Consignment no. :

Offer no. :

Project :

Remarks :

### Engineering data

Rated speed	2000 rpm
Rated torque (100 K)	16.70 Nm
Rated current	11.0 A
Rated power	3.50 kW / 4.76 hp
Max. speed	3000 rpm
Maximum torque	50.00 Nm
Max. current	32.9 A
Static torque	22.00 Nm
Moment of inertia	77.900 kgcm <sup>2</sup>

### Physical constants

Torque constant	1.60 Nm/A
Thermal class	B (130 °C)
Net weight	25.90 kg

### Ambient conditions

#### Ambient temperature

Operation	0 ... 40 °C
-----------	-------------

#### Relative humidity

Max. operation	90 % RH maximum (no condensation at 30 °C)
----------------	--

### Standards

Compliance with standards	CE, EAC
---------------------------	---------

### Mechanical data

Motor type	High Inertia
Motor type	Permanent-magnet synchronous motor
Shaft height	90
Encoder system	Incremental encoder TTL, 2500 S/R (13 bit)
Cooling	Natural cooling
Shaft end	Feather key
Radial runout tolerance	Class N
Vibration severity grade	Grade A
Degree of protection	IP65
Design acc. to Code I	IM B5 (IM V1, IM V3)
Connection type	Angular connector (rotatable)

### Holding brake

Holding torque $M_{4Br}$	30.00 Nm
Rated voltage	24 V DC 10 %
	220 ms
	115 ms
Rated current	1.90 A