



Figure similar

MLFB-Ordering data

6FX2001-5FD13-1AA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Electrical data

Operating voltage Up	DC 24 V - 15 % + 20 %
Max. power consumption	37 mA
Interface	DRIVE-CLiQ
Data output	DRIVE-CLiQ
Short-circuit strength	Yes
Transmission rate	100 Mbit/s
Cable length up to the subsequent electronics, max.	100 m
Connection type	Flange socket, Radial
Resolution	24 bit
Incremental track	2048 S/R, 1 Vpp (encoder-internal only)
Accuracy	± 20 "
Code type	
Sampling	Gray
Transmission	DRIVE-CLiQ

Ambient temperature

During operation	-30 ... 100 °C
------------------	----------------

Standards

Compliance with standards	CE, cULus
EMC class filter	Tested to DIN EN 50081 and EN 50082

Mechanical data

Shaft version	Solid shaft
Shaft diameter	6 mm
Shaft length	10 mm
Angular acceleration, max.	100000 rad/s ²
Moment of inertia of rotor	0.00000290 kgm ²
Vibration (55...2000 Hz), max.	300 m/s ²
Friction torque (at 20°C)	≤ 0.01 Nm
Starting torque (at 20°C)	≤ 0.01 Nm

Net weight	0.3 kg
------------	--------

Max. admissible speed

Electrical	14000 rpm
Mechanical	15000 rpm

Load capacity

n = 6000 rpm	
- Axial	10 N
- Radial at shaft end	20 N
n > 6000 rpm	
- Axial	40 N
- Radial at shaft end	60 N

Shock, max.

6 ms	2000 m/s ²
------	-----------------------

Degree of protection

Without shaft input	IP67
With shaft input	IP64