

Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1AV2133C

SIMOTICS GP - 132 M - IM B3 - 6p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	Project
Remarks		

Electrical data

Safe Area

U [V]	Δ / Y	f [Hz]	P [kW]	P [hp]	I [A]	n [1/min]	M [Nm]	η ³⁾			$\cos\phi$ ³⁾			I_A/I_N I_i/I_N	M_A/M_N T_i/T_N	M_K/M_N T_B/T_N	IE-CL
								4/4	3/4	2/4	4/4	3/4	2/4				
DOL duty (S1) - 155(F) to 130(B)																	
400	Δ	50	5.50	-/-	12.10	970	54.0	86.0	87.1	86.4	0.76	0.69	0.56	5.6	1.9	2.6	IE2
690	Y	50	5.50	-/-	7.00	970	54.0	86.0	87.1	86.4	0.76	0.69	0.56	5.6	1.9	2.6	IE2
460	Δ	60	6.30	-/-	11.60	1170	51.0	89.5	90.6	90.2	0.76	0.70	0.59	5.8	1.9	2.6	IE2
460	Δ	60	5.50	-/-	10.60	1175	44.5	89.5	89.9	88.9	0.73	0.66	0.54	6.5	2.1	2.9	IE2
IM B3 / IM 1001		FS 132 M		IP55		IEC/EN 60034		IEC, DIN, ISO, VDE, EN									
Environmental conditions : -20 °C - +40 °C / 1,000 m										Locked rotor time (hot / cold) : 19.5 s 32.7 s							

Mechanical data

Sound level (SPL / SWL) at 50Hz 60Hz	63 / 75 dB(A) ²⁾	67 / 79 dB(A) ²⁾	Vibration severity grade	A
Moment of inertia	0.0370 kg m ²		Thermal class	F
Bearing DE NDE	6208 2Z C3	6208 2Z C3	Duty type	S1
bearing lifetime			Direction of rotation	bidirectional
L_{10mh} , F_{Rad} , m_{min} for coupling operation 50 60Hz	40000 h	32000 h	Frame material	aluminum
Lubricants	Unirex N3		Net weight of the motor (IM B3)	52 kg
Regreasing device	No		Coating (paint finish)	Standard paint finish C2
Grease nipple	-/-		Color, paint shade	RAL7030
Type of bearing	Preloaded bearing DE		Motor protection	(A) without (Standard)
Condensate drainage holes	No		Method of cooling	IC411 - self ventilated, surface cooled
External earthing terminal	No			

Terminal box

Terminal box position	top	Max. cross-sectional area	6 mm ²
Material of terminal box	Aluminium	Cable diameter from ... to ...	11 mm - 21 mm
Type of terminal box	TB1 H00	Cable entry	2xM32x1,5
Contact screw thread	M4	Cable gland	2 plugs

Notes:

I_A/I_N = locked rotor current / current nominal
 M_A/M_N = locked rotor torque / torque nominal
 M_K/M_N = break down torque / nominal torque
 1) L10mh according to DIN ISO 281 10/2010
 2) at rated power / at full load
 3) Value is valid only for DOL operation with motor design IC411

responsible dep. DI MC LVM	technical reference	created by DT Configurator	approved by	<i>Technical data are subject to change! There may be discrepancies between calculated and rating plate values.</i>	Link documents
	document type datasheet	document status released			
	title 1LE1001-1CC33-4AA4	document number			
© Siemens AG 2021	rev. 01	creation date 2021-11-28	language en		