

# Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1AV1130C

SIMOTICS GP - 132 S - IM B3 - 6p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	project

Remarks

## Electrical data

## Safe Area

U [V]	$\Delta / Y$	f [Hz]	P [kW]	P [hp]	I [A]	n [1/min]	M [Nm]	$\eta$ <sup>3)</sup>			$\cos\phi$ <sup>3)</sup>			$I_A/I_N$ $I_i/I_N$	$M_A/M_N$ $T_i/T_N$	$M_K/M_N$ $T_B/T_N$	IE-CL
								4/4	3/4	2/4	4/4	3/4	2/4				
400	$\Delta$	50	3.00	-/-	7.30	955	30.0	79.7	79.9	77.1	0.74	0.66	0.52	4.6	2.0	2.6	IE1
690	Y	50	3.00	-/-	4.25	955	30.0	79.7	79.9	77.1	0.74	0.66	0.52	4.6	2.0	2.6	IE1
460	$\Delta$	60	3.45	-/-	6.90	1150	28.5	83.5	83.7	81.4	0.75	0.67	0.55	4.6	1.9	2.3	IE1
IM B3 / IM 1001		FS 132 S		34 kg		IP55		IEC/EN 60034			IEC, DIN, ISO, VDE, EN						

Environmental conditions : -20 °C - +40 °C / 1,000 m

## Mechanical data

Sound level (SPL / SWL) at 50Hz 60Hz	63.0 / 75.0 dB(A) <sup>2)</sup>	67.0 / 79.0 dB(A) <sup>2)</sup>	External earthing terminal	No
Moment of inertia	0.0170 kg m <sup>2</sup>		Vibration severity grade	A
Bearing DE   NDE	6208 2Z C3	6208 2Z C3	Insulation	155(F) to 130(B)
<b>bearing lifetime</b>			Duty type	S1
L <sub>10mh</sub> F <sub>Rad min</sub> for coupling operation 50 60Hz <sup>1)</sup>	40000 h	32000 h	Direction of rotation	bidirectional
Lubricants	Unirex N3		Frame material	aluminum
Regreasing device	No		Coating (paint finish)	Standard paint finish C2
Grease nipple	-/-		Color, paint shade	RAL7030
Type of bearing	Preloaded bearing DE		Motor protection	(A) without (Standard)
Condensate drainage holes	No		Method of cooling	IC411 - self ventilated, surface cooled

## Terminal box

Terminal box position	top	Max. cross-sectional area	6.0 mm <sup>2</sup>
Material of terminal box	Aluminium	Cable diameter from ... to ...	11.0 mm - 21.0 mm
Type of terminal box	TB1 H00	Cable entry	2xM32x1,5
Contact screw thread	M4	Cable gland	2 plugs

### Notes:

$I_A/I_N$  = locked rotor current / current nominal  
 $M_A/M_N$  = locked rotor torque / torque nominal  
 $M_K/M_N$  = break down torque / nominal torque  
 1) L10mh according to DIN ISO 281 10/2010  
 2) at rated power / at full load  
 3) Value is valid only for DOL operation with motor design IC411

responsible dep. DI MC LVM	technical reference	created by DT Configurator	approved by	<i>Technical data are subject to change! There may be discrepancies between calculated and rating plate values.</i>			
<b>SIEMENS</b>	document type datasheet	document status released		customer			
	title 1LE1002-1CC03-4AA4	document number					
© Siemens AG 2021	rev. 01	creation date 2021-01-17 21:10	language en	Page 1/1			