

Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1AV3162B

SIMOTICS GP - 160 M - IM B5 - 4p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	Project
Remarks		

Electrical data

Safe Area

U [V]	Δ / Y	f [Hz]	P [kW]	P [hp]	I [A]	n [1/min]	M [Nm]	η ³⁾			$\cos\phi$ ³⁾			I_A/I_N I_f/I_N	M_A/M_N T_f/T_N	M_K/M_N T_B/T_N	IE-CL
								4/4	3/4	2/4	4/4	3/4	2/4				
DOL duty (S1) - 155(F) to 130(B)																	
400	Δ	50	11.00	-/-	21.00	1470	71.0	91.4	91.9	91.9	0.82	0.76	0.65	8.0	2.5	3.5	IE3
690	Y	50	11.00	-/-	12.30	1470	71.0	91.4	91.9	91.9	0.82	0.76	0.65	8.0	2.5	3.5	IE3
460	Δ	60	12.60	-/-	20.50	1765	68.0	92.4	92.9	92.6	0.83	0.78	0.68	8.1	3.3	3.5	IE3
460	Δ	60	11.00	-/-	18.40	1775	59.0	92.4	92.6	92.0	0.81	0.75	0.63	9.0	3.8	4.0	IE3
IM B5 / IM 3001		FS 160 M		IP55		UKCA		IEC/EN 60034			IEC, DIN, ISO, VDE, EN						
Environmental conditions : -20 °C - +40 °C / 1,000 m										Locked rotor time (hot / cold) : 26.5 s 34.3 s							

Mechanical data

Sound level (SPL / SWL) at 50Hz 60Hz	65 / 77 dB(A) ^{2) 3)}	69 / 81 dB(A) ^{2) 3)}	Vibration severity grade	A
Moment of inertia	0.0583 kg m ²		Thermal class	F
Bearing DE NDE	6209 2Z C3	6209 2Z C3	Duty type	S1
bearing lifetime			Direction of rotation	bidirectional
L_{10mh} , $F_{Rad min}$ 50 60Hz ¹⁾ for coupling operation	40000 h	32000 h	Frame material	aluminum
Regreasing device	No		Net weight of the motor (IM B3)	78 kg
Grease nipple	-/-		Coating (paint finish)	Standard paint finish C2
Type of bearing	Locating bearing NDE		Color, paint shade	RAL7030
Condensate drainage holes	No		Motor protection	(B) 3 PTC thermistors - for tripping (2 terminals)
External earthing terminal	No		Method of cooling	IC411 - self ventilated, surface cooled

Terminal box

Terminal box position	top	Max. cross-sectional area	16 mm ²
Material of terminal box	Aluminium	Cable diameter from ... to ...	19 mm - 28 mm
Type of terminal box	TB1 J00	Cable entry	2xM40x1,5-1xM16x1,5
Contact screw thread	M5	Cable gland	3 plugs

Notes:
 I_A/I_N = locked rotor current / current nominal
 M_A/M_N = locked rotor torque / torque nominal
 M_K/M_N = break down torque / nominal torque
 1) L10mh according to DIN ISO 281 10/2010
 2) at rated power / at full load
 3) Value is valid only for DOL operation with motor design IC411

responsible dep. DI MC LVM	technical reference	created by DT Configurator	approved by	<i>Technical data are subject to change! There may be discrepancies between calculated and rating plate values.</i>	Link documents
	document type datasheet	document status released			document number
	title 1LE1003-1DB23-4FB4	rev. 929	creation date 2022-12-04		
© Siemens AG 2022					