

Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1CV1184B

SIMOTICS SD - 180 L - IM B3 - 4p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	project

Remarks

Electrical data

Safe Area

U [V]	Δ / Y	f [Hz]	P [kW]	P [hp]	I [A]	n [1/min]	M [Nm]	η ³⁾			$\cos\phi$ ³⁾			I_A/I_N I_i/I_N	M_A/M_N T_i/T_N	M_k/M_N T_B/T_N	IE-CL
								4/4	3/4	2/4	4/4	3/4	2/4				
400	Δ	50	22.00	-/-	42.50	1465	143.0	89.9	90.8	90.7	0.83	0.78	0.67	8.0	2.7	3.6	IE1
690	Y	50	22.00	-/-	24.50	1465	143.0	89.9	90.8	90.7	0.83	0.78	0.67	8.0	2.7	3.6	IE1
460	Δ	60	25.30	-/-	41.50	1765	137.0	91.0	91.7	91.5	0.84	0.79	0.69	8.2	2.7	3.6	IE1

IM B3 / IM 1001	FS 180 L	170 kg	IP55	IEC/EN 60034	IEC, DIN, ISO, VDE, EN
-----------------	----------	--------	------	--------------	------------------------

Environmental conditions : -20 °C - +40 °C / 1,000 m

Mechanical data

Sound level (SPL / SWL) at 50Hz 60Hz	63.0 / 76.0 dB(A) ²⁾	66.0 / 79.0 dB(A) ²⁾	External earthing terminal	Yes (standard)
Moment of inertia	0.1300 kg m ²		Vibration severity grade	A
Bearing DE NDE	6210 Z C3	6210 Z C3	Insulation	155(F) to 130(B)
bearing lifetime			Duty type	S1
L _{10mh} F _{Rad min} for coupling operation 50 60Hz ¹⁾	40000 h	32000 h	Direction of rotation	bidirectional
Lubricants	Unirex N3		Frame material	cast iron
Regreasing device	No		Coating (paint finish)	Standard paint finish C2
Grease nipple	-/-		Color, paint shade	RAL7030
Type of bearing	Locating bearing NDE		Motor protection	(A) without (Standard)
Condensate drainage holes	Yes (standard)		Method of cooling	IC411 - self ventilated, surface cooled


Terminal box

Terminal box position	top	Max. cross-sectional area	16.0 mm ²
Material of terminal box	cast iron	Cable diameter from ... to ...	19.0 mm - 28.0 mm
Type of terminal box	TB1 J01	Cable entry	2xM40x1,5
Contact screw thread	M5	Cable gland	2 plugs

Notes:

I_A/I_N = locked rotor current / current nominal
 M_k/M_N = locked rotor torque / torque nominal
 M_k/M_N = break down torque / nominal torque
 1) L10mh according to DIN ISO 281 10/2010
 2) at rated power / at full load
 3) Value is valid only for DOL operation with motor design IC411

responsible dep. DI MC LVM	technical reference	created by DT Configurator	approved by	<i>Technical data are subject to change! There may be discrepancies between calculated and rating plate values.</i>
-------------------------------	---------------------	-------------------------------	-------------	---

	document type datasheet	document status released	customer	
	title 1LE1502-1EB43-4AA4	document number	rev. 01	creation date 2021-01-17 20:55
© Siemens AG 2021				Page 1/1