



Figure similar

### MLFB-Ordering data

6SE6440-2UD41-6GA1

Client order no. :

Item no. :

Order no. :

Consignment no. :

Offer no. :

Project :

Remarks :

### Rated data

#### Input

Number of phases	3 AC
Line voltage	380 ... 480 V $\pm$ 10 %
Line frequency	47 ... 63 Hz
Rated current (LO)	354.00 A
Rated current (HO)	297.00 A

#### Output

Number of phases	3 AC
Rated voltage	480 V
Rated power (LO)	200.00 kW / 300.00 hp
Rated power (HO)	160.00 kW / 250.00 hp
Rated current (LO)	370.00 A
Rated current (HO)	302.00 A
Pulse frequency	4000 Hz
Output frequency for V/f control	0 ... 267 Hz

### General tech. specifications

Power factor $\lambda$	0.95
Efficiency $\eta$	0.97

### Ambient conditions

Cooling	Fan
<b>Ambient temperature</b>	
Operation (LO)	0 ... 40 °C
Operation (HO)	0 ... 40 °C
Transport	-40 ... 70 °C
Storage	-40 ... 70 °C

### Overload capability

#### Low Overload (LO)

150 % output current for 1 s, followed by 110 % output current for 59 s followed by 100 % output current for 240 s in a 300 s cycle time

#### High Overload (HO)

136 % output current for 57 s, followed by 100 % output current for 243 s in a 300 s cycle time

MLFB-Ordering data

6SE6440-2UD41-6GA1



Figure similar

### Mechanical data

Degree of protection	IP20 / UL open type
Size	FSGX
Net weight	174.00 kg
Width	326.0 mm
Height	1533.0 mm
Depth	545.0 mm

### Connections

#### Motor end

Conductor cross-section	240.00 mm <sup>2</sup>
-------------------------	------------------------

### Inputs / outputs

#### Standard digital inputs

Number	6
--------	---

#### Relay output

Number	3
--------	---

#### Analog inputs

Number	2
--------	---

#### Analog outputs

Number	2
--------	---

#### PTC/ KTY interface

Number	1
--------	---