



Figure similar

### MLFB-Ordering data

6SL3210-1PE21-4AL0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data	General tech. specifications
------------	------------------------------

### Input

Number of phases	3 AC
Line voltage	380 ... 480 V $\pm$ 10 %
Line frequency	47 ... 63 Hz
Rated current (LO)	17.20 A
Rated current (HO)	15.30 A

### Output

Number of phases	3 AC
Rated voltage	400 V
Rated current (LO)	13.20 A
Rated current (HO)	10.20 A
Max. output current	20.40 A
Rated power IEC 400V (LO)	5.50 kW
Rated power NEC 480V (LO)	7.50 hp
Rated power IEC 400V (HO)	4.00 kW
Rated power NEC 480V (HO)	5.00 hp
Pulse frequency	4 kHz
Output frequency for vector control	0 ... 200 Hz
Output frequency for V/f control	0 ... 550 Hz

### Overload capability

#### Low Overload (LO)

1.1 x rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s 1.5 x rated output current (i.e. 150 % overload) for 3 s with a cycle time of 300 s

#### High Overload (HO)

1.5 x output current rating (i.e., 150 % overload) for 57 s with a cycle time of 300 s 2 x output current rating (i.e., 200 % overload) for 3 s with a cycle time of 300 s

Power factor $\lambda$	0.85
Offset factor $\cos \varphi$	0.95
Efficiency $\eta$	0.97
Sound pressure level (1m)	72 dB
Power loss	0.15 kW
Filter class (integrated)	Class A

### Ambient conditions

Cooling	Internal air cooling
Cooling air requirement	0.009 m <sup>3</sup> /s (0.325 ft <sup>3</sup> /s)
Installation altitude	1000 m (3280.84 ft)
<b>Ambient temperature</b>	
Operation LO	-5 ... 40 °C (23 ... 104 °F)
Operation HO	-5 ... 50 °C (23 ... 122 °F)
Transport	-25 ... 55 °C (-13 ... 131 °F)
Storage	-25 ... 55 °C (-13 ... 131 °F)

### Relative humidity

Max. operation	95 % RH, condensation not permitted
----------------	-------------------------------------



Figure similar

MLFB-Ordering data

6SL3210-1PE21-4AL0

### Mechanical data

Degree of protection	IP20 / UL open type
Size	FSB
Net weight	3.10 kg (6.83 lb)
Width	100 mm (3.94 in)
Height	292 mm (11.50 in)
Depth	165 mm (6.50 in)

### Connections

#### Line side


Version	Plug-in screw terminals
Conductor cross-section	1.50 ... 6.00 mm <sup>2</sup> (AWG 16 ... AWG 10)

#### Motor end

Version	Plug-in screw terminals
Conductor cross-section	1.50 ... 6.00 mm <sup>2</sup> (AWG 16 ... AWG 10)

### Converter losses to EN 50598-2\*

Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	-65.72 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

### Max. motor cable length

Shielded	50 m (164.04 ft)
Unshielded	100 m (328.08 ft)

### Standards

Compliance with standards: UL, cUL, CE, C-Tick (RCM), SEMI F47

CE marking: Low-voltage directive 2006/95/EC