



Figure similar

Article No. : 6SL3120-1TE31-3AA3

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

DC link voltage	DC 510 ... 720 V
Electronics power supply	DC 24 V -15 % / +20 %
Current demand, max.	1.50 A
DC-link current I_d	158.0 A

Output current

Rated value I_N	132.0 A
Base load current I_H	105.0 A
For S6 duty (40%) I_{S6}	150.0 A
I_{max}	210.0 A

Type rating²⁾

Based on I_N	71.0 kW
Based on I_H	57.0 kW
Rated pulse frequency	4.00 kHz

Current carrying capacity

DC link busbars	200 A
24 V busbars	20 A
DC link capacitance	2,820 μ F
Output frequency for servo control ⁵⁾	0 ... 650 Hz
Output frequency for V/f control ⁶⁾	0 ... 600 Hz
Output frequency for vector control ⁷⁾	0 ... 300 Hz

Ambient conditions

Installation altitude (without derating)	1,000 m (3,281 ft)
Cooling ⁸⁾	Internal air cooling
Cooling air requirement	0.144 m ³ /s

Ambient temperature

During operation	0 ... 40 °C (32 ... 104 °F)
------------------	-----------------------------

Connections

Motor end

Version	M8 bolt (X1)
Conductor cross-section	2.5 ... 120 mm ² (14 ... -3 AWG)
PE connection	M8 Screw

Max. motor cable length

Shielded	100 m (328 ft)
Unshielded	150 m (492 ft)

Standards

Compliance with standards	CE, cULus
Safety Integrated	SIL 2 acc. to IEC 61508, PL d acc. to EN ISO 13849-1, Category 3 acc. to EN ISO 13849-1

Mechanical data

Line side

Width	300.00 mm (11.81 in)
Height	629.00 mm (24.76 in)
Depth	270.00 mm (10.63 in)
Degree of protection	IP20 / UL open type
Type of construction	Booksize
Net weight	21.0 kg (46.30 lb)

General tech. specifications

Sound pressure level (1m)	73.0 dB
Power loss, typ./max. ⁹⁾	1.26 kW / 1.29 kW

²⁾Rated output of a typical standard asynchronous motor at 400 V 3 AC

⁵⁾With rated output current (max. output frequency 1300 Hz at a current controller cycle of 62.5 μ s, pulse frequency 8 kHz, 60 % permissible output current). Observe the dependency between max. output frequency and current derating. At present, the output frequency is limited to 550 Hz, the values stated apply with the high output frequency license.

⁶⁾Observe the dependency between max. output frequency and current derating. At present, the output frequency is limited to 550 Hz, the values stated apply with the high output frequency license.

⁷⁾Observe the dependency between max. output frequency and current derating.

⁸⁾Power units with intensified air cooling thanks to integrated fan

⁹⁾Power loss of the Motor Module with rated power including losses of the 24 V DC electronics power supply