

Article No. : 6SL3210-5BE23-0UV0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Rated data

| | |
|------------------|---------------------------|
| Input | |
| Number of phases | 3 AC |
| Line voltage | 380 ... 480 V -15 % +10 % |
| Line frequency | 47 ... 63 Hz |

| | |
|--------------------|--------------------------------------|
| Output | |
| Number of phases | 3 AC |
| Rated voltage | 400V IEC 480V NEC ¹⁾ |
| Rated power (LO) | 3.00 kW 4.00 hp |
| Rated power (HO) | 3.00 kW 4.00 hp |
| Rated current (LO) | 7.30 A 7.30 A |
| Rated current (HO) | 7.30 A 7.30 A |
| Rated current (IN) | 7.30 A |
| Pulse frequency | 4.00 kHz |
| Output frequency | 0 ... 550 Hz |

| | |
|---|--|
| Overload capability | |
| Low Overload (LO) | |
| 110 % rated output current for 60 s, cycle time 300 s | |
| High Overload (HO) | |
| 150 % rated output current for 60 s, cycle time 300 s | |

| | |
|------------------------------|------------|
| General tech. specifications | |
| Power factor λ | 0.72 |
| Offset factor cos φ | 0.95 |
| Efficiency η | 0.98 |
| Filter class (integrated) | Unfiltered |

| | |
|---------------|-----------------|
| Communication | |
| Communication | USS, Modbus RTU |

Inputs / outputs

| | |
|-------------------------|---|
| Standard digital inputs | |
| Number | 4 |

| | |
|------------------------------------|---|
| Digital outputs | |
| Number as relay changeover contact | 1 |
| Number as transistor | 1 |

| | |
|---------------|---|
| Analog inputs | |
| Number | 2 (Can be used as additional digital input) |

| | |
|----------------|---|
| Analog outputs | |
| Number | 1 |

Ambient conditions

| | |
|-----------------------|-----------------------|
| Cooling | External fan |
| Installation altitude | 1,000 m (3,280.84 ft) |

| | |
|-------------------------|--------------------------------|
| Ambient temperature | |
| Operation ²⁾ | -10 ... 60 °C (14 ... 140 °F) |
| Storage | -40 ... 70 °C (-40 ... 158 °F) |

| | |
|-------------------|------|
| Relative humidity | |
| Max. operation | 95 % |

Connections

| | |
|-------------------------|------------------|
| Max. motor cable length | |
| Shielded | 25 m (82.02 ft) |
| Unshielded | 50 m (164.04 ft) |

| | |
|----------------------|---|
| Mechanical data | |
| Mounting position | Through-hole mounting / wall mounting / side-by-side mounting |
| Degree of protection | IP20 / UL open type |
| Frame size | FSB |
| Net weight | 1.60 kg (3.53 lb) |


| | |
|------------|--------------------|
| Dimensions | |
| Width | 140.0 mm (5.51 in) |
| Height | 160.0 mm (6.30 in) |
| Depth | 164.5 mm (6.48 in) |

| | |
|---------------------------|---|
| Standards | |
| Compliance with standards | CE, cULus, C-Tick (RCM), KC |
| CE marking | EN 61800-5-1 /EN 60204-1 and EN 61800-3 |

Data sheet for SINAMICS V20

Article No. : 6SL3210-5BE23-0UV0

| Converter losses to IEC61800-9-2 * | |
|--|--------|
| Efficiency class | IE2 |
| Comparison with the reference converter (90% / 100%) | 33.4 % |



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*calculated values

¹⁾ The output current and HP ratings are valid for the voltage range 440V-480V

²⁾ Please observe derating at temperatures of 40 °C or above