



Figure similar

MLFB-Ordering data

6SL3210-1PB21-8UL0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data

Input

Number of phases	1 AC
Line voltage	200 ... 240 V \pm 10 %
Line frequency	47 ... 63 Hz
Rated current (LO)	43.00 A / 24.80 A
Rated current (HO)	37.50 A / 21.70 A

Output

Number of phases	3 AC
Rated voltage	230 V
Rated current (LO)	17.50 A
Rated current (HO)	13.60 A
Max. output current	27.20 A
Rated power IEC 230V (LO)	4.00 kW
Rated power NEC 240V (LO)	5.00 hp
Rated power IEC 230V (HO)	3.00 kW
Rated power NEC 240V (HO)	4.00 hp
Pulse frequency	4 kHz
Output frequency for vector control	0 ... 200 Hz
Output frequency for V/f control	0 ... 550 Hz

Overload capability

Low Overload (LO)

1.1 x rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s 1.5 x rated output current (i.e. 150 % overload) for 3 s with a cycle time of 300 s

High Overload (HO)

1.5 x output current rating (i.e., 150 % overload) for 57 s with a cycle time of 300 s 2 x output current rating (i.e., 200 % overload) for 3 s with a cycle time of 300 s

General tech. specifications

Power factor λ	0.85
Offset factor $\cos \phi$	0.95
Efficiency η	0.96
Sound pressure level (1m)	65 dB
Power loss	0.18 kW
Filter class (integrated)	-

Ambient conditions

Cooling	Internal air cooling
Cooling air requirement	0.018 m ³ /s (0.653 ft ³ /s)
Installation altitude	1000 m (3280.84 ft)
Ambient temperature	
Operation LO	-5 ... 40 °C (23 ... 104 °F)
Operation HO	-5 ... 50 °C (23 ... 122 °F)
Transport	-25 ... 55 °C (-13 ... 131 °F)
Storage	-25 ... 55 °C (-13 ... 131 °F)

Relative humidity

Max. operation	95 % RH, condensation not permitted
----------------	-------------------------------------



Figure similar

MLFB-Ordering data

6SL3210-1PB21-8UL0


Mechanical data	
Degree of protection	IP20 / UL open type
Size	FSC
Net weight	5.00 kg (11.02 lb)
Width	140 mm (5.51 in)
Height	355 mm (13.98 in)
Depth	165 mm (6.50 in)

Connections	
Line side	
Version	Plug-in screw terminals
Conductor cross-section	6.00 ... 16.00 mm ² (AWG 10 ... AWG 6)
Motor end	
Version	Plug-in screw terminals
Conductor cross-section	6.00 ... 16.00 mm ² (AWG 10 ... AWG 6)

Converter losses to EN 50598-2*

Efficiency class ?PMD_ACF685_001_00 ?

Comparison with the reference converter (90% / 100%) -47.64 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

Max. motor cable length

Shielded	50 m (164.04 ft)
Unshielded	100 m (328.08 ft)

Standards

Compliance with standards UL, cUL, CE, C-Tick (RCM), SEMI F47

CE marking Low-voltage directive 2006/95/EC