

Article No. : 6SL3210-1PE16-1AL1



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

Input

| | |
|--------------------|--------------------------|
| Number of phases | 3 AC |
| Line voltage | 380 ... 480 V \pm 10 % |
| Line frequency | 47 ... 63 Hz |
| Rated current (LO) | 7.70 A |
| Rated current (HO) | 6.10 A |

Output

| | | |
|-------------------------------------|-----------------|-------------------------------|
| Number of phases | 3 AC | |
| Rated voltage | 400V IEC | 480V NEC ¹⁾ |
| Rated power (LO) | 2.20 kW | 3.00 hp |
| Rated power (HO) | 1.50 kW | 2.00 hp |
| Rated current (LO) | 5.90 A | |
| Rated current (HO) | 4.10 A | |
| Max. output current | 8.90 A | |
| Pulse frequency | 4 kHz | |
| Output frequency for vector control | 0 ... 200 Hz | |
| Output frequency for V/f control | 0 ... 550 Hz | |

Overload capability

Low Overload (LO)

1.1 x rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s
1.5 x rated output current (i.e. 150 % overload) for 3 s with a cycle time of 300 s

High Overload (HO)

1.5 x output current rating (i.e., 150 % overload) for 57 s with a cycle time of 300 s
2 x output current rating (i.e., 200 % overload) for 3 s with a cycle time of 300 s

General tech. specifications

| | |
|------------------------------|---------|
| Power factor λ | 0.85 |
| Offset factor $\cos \varphi$ | 0.95 |
| Efficiency η | 0.96 |
| Sound pressure level (1m) | 72 dB |
| Power loss | 0.10 kW |
| Filter class (integrated) | Class A |

Ambient conditions

| | |
|-------------------------|--|
| Cooling | Internal air cooling |
| Cooling air requirement | 0.005 m ³ /s (0.177 ft ³ /s) |
| Installation altitude | 1,000 m (3,280.84 ft) |

Ambient temperature

| | |
|--------------|--------------------------------|
| Operation LO | -10 ... 40 °C (14 ... 104 °F) |
| Operation HO | -10 ... 50 °C (14 ... 122 °F) |
| Transport | -25 ... 55 °C (-13 ... 131 °F) |
| Storage | -25 ... 55 °C (-13 ... 131 °F) |

Relative humidity

| | |
|----------------|-------------------------------------|
| Max. operation | 95 % RH, condensation not permitted |
|----------------|-------------------------------------|

Connections

Line side

| | |
|-------------------------|--|
| Version | Plug-in screw terminals |
| Conductor cross-section | 1.50 ... 2.50 mm ² (AWG 16 ... AWG 14) |

Motor end

| | |
|-------------------------|--|
| Version | Plug-in screw terminals |
| Conductor cross-section | 1.50 ... 2.50 mm ² (AWG 16 ... AWG 14) |

Max. motor cable length

| | |
|------------|-------------------|
| Shielded | 50 m (164.04 ft) |
| Unshielded | 100 m (328.08 ft) |

Mechanical data

| | |
|----------------------|---------------------|
| Degree of protection | IP20 / UL open type |
| Frame size | FSA |
| Net weight | 1.50 kg (3.31 lb) |

Dimensions

| | |
|--------|------------------|
| Width | 73 mm (2.87 in) |
| Height | 196 mm (7.72 in) |
| Depth | 165 mm (6.50 in) |

Standards


| | |
|---------------------------|-------------------------------------|
| Compliance with standards | UL, cUL, CE, C-Tick (RCM), SEMI F47 |
| CE marking | Low-voltage directive 2006/95/EC |

Data sheet for SINAMICS Power module PM240-2

Article No. : 6SL3210-1PE16-1AL1

Converter losses to IEC61800-9-2*

| | |
|--|---------|
| Efficiency class | IE2 |
| Comparison with the reference converter (90% / 100%) | 29.80 % |



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*calculated values

¹⁾The output current and HP ratings are valid for the voltage range 440V-480V