



Figure similar

### MLFB-Ordering data

6SL3220-3YH58-0CP0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

| Rated data | General tech. specifications |
|------------|------------------------------|
|------------|------------------------------|

#### Input

|                    |                           |          |
|--------------------|---------------------------|----------|
| Number of phases   | 3 AC                      |          |
| Line voltage       | 500 ... 690 V +10 % -10 % |          |
| Line frequency     | 47 ... 63 Hz              |          |
| Rated voltage      | 690V IEC                  | 600V NEC |
| Rated current (LO) | 416.00 A                  | 408.00 A |
| Rated current (HO) | 327.00 A                  | 333.00 A |

#### Output

|                                     |              |           |
|-------------------------------------|--------------|-----------|
| Number of phases                    | 3 AC         |           |
| Rated voltage                       | 690V IEC     | 600V NEC  |
| Rated power (LO)                    | 355.00 kW    | 400.00 hp |
| Rated power (HO)                    | 315.00 kW    | 350.00 hp |
| Rated current (LO)                  | 385.00 A     | 388.00 A  |
| Rated current (HO)                  | 330.00 A     | 320.00 A  |
| Rated current (IN)                  | 400.00 A     |           |
| Max. output current                 | 529.00 A     |           |
| Pulse frequency                     | 2 kHz        |           |
| Output frequency for vector control | 0 ... 100 Hz |           |
| Output frequency for V/f control    | 0 ... 100 Hz |           |

#### Overload capability

##### Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

##### High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

|                                 |  |
|---------------------------------|--|
| Power factor $\lambda$          | 0.75 ... 0.93                          |
| Offset factor $\cos \phi$       | 0.96                                   |
| Efficiency $\eta$               | 0.98                                   |
| Sound pressure level (1m)       | 74 dB                                  |
| Power loss                      | 6.191 kW                               |
| Filter class (integrated)       | RFI suppression filter for Category C3 |
| EMC category (with accessories) | Category C3                            |

#### Ambient conditions

|                             |   |
|-----------------------------|---|
| Standard board coating type | Class 3C2, according to IEC 60721-3-3: 2002         |
| Cooling                     | Air cooling using an integrated fan                 |
| Cooling air requirement     | 0.362 m <sup>3</sup> /s (12.784 ft <sup>3</sup> /s) |
| Installation altitude       | 1000 m (3280.84 ft)                                 |
| Ambient temperature         |   |
| Operation                   | 0 ... 45 °C (32 ... 113 °F)                         |
| Transport                   | -40 ... 70 °C (-40 ... 158 °F)                      |
| Storage                     | -25 ... 55 °C (-13 ... 131 °F)                      |

#### Relative humidity

|                |  |
|----------------|--|
| Max. operation | 95 % At 40 °C (104 °F), condensation and icing not permissible |
|----------------|--|



Figure similar

MLFB-Ordering data

6SL3220-3YH58-0CP0

### Mechanical data

|                      |                     |
|----------------------|---------------------|
| Degree of protection | IP20 / UL open type |
| Size                 | FSH                 |
| Net weight           | 158 kg (348.33 lb)  |
| Width                | 548 mm (21.57 in)   |
| Height               | 1695 mm (66.73 in)  |
| Depth                | 393 mm (15.47 in)   |

### Inputs / outputs

#### Standard digital inputs

|                      |       |
|----------------------|-------|
| Number               | 6     |
| Switching level: 0→1 | 11 V  |
| Switching level: 1→0 | 5 V   |
| Max. inrush current  | 15 mA |

#### Fail-safe digital inputs

|        |   |
|--------|---|
| Number | 1 |
|--------|---|

#### Digital outputs

|                                    |                |
|------------------------------------|----------------|
| Number as relay changeover contact | 2              |
| Output (resistive load)            | DC 30 V, 5.0 A |
| Number as transistor               | 0              |

#### Analog / digital inputs

|            |                        |
|------------|------------------------|
| Number     | 2 (Differential input) |
| Resolution | 10 bit                 |

#### Switching threshold as digital input

|     |       |
|-----|-------|
| 0→1 | 4 V   |
| 1→0 | 1.6 V |

#### Analog outputs

|        |                         |
|--------|-------------------------|
| Number | 1 (Non-isolated output) |
|--------|-------------------------|

#### PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected: PTC, KTY and Thermo-Click, accuracy ±5 °C

### Closed-loop control techniques

|   |     |
|---|-----|
| V/f linear / square-law / parameterizable | Yes |
| V/f with flux current control (FCC)       | Yes |
| V/f ECO linear / square-law               | Yes |
| Sensorless vector control                 | Yes |
| Vector control, with sensor               | No  |
| Encoderless torque control                | Yes |
| Torque control, with encoder              | No  |

### Communication

|               |             |
|---------------|-------------|
| Communication | PROFIBUS DP |
|---------------|-------------|

### Connections

#### Signal cable

|                         |  |
|-------------------------|--|
| Conductor cross-section | 0.15 ... 1.50 mm <sup>2</sup><br>(AWG 24 ... AWG 16) |
|-------------------------|--|

#### Line side

|                         |  |
|-------------------------|--|
| Version                 | M12 screw  |
| Conductor cross-section | 35.00 ... 240.00 mm <sup>2</sup><br>(AWG 2 ... AWG -3) |

#### Motor end

|                         |  |
|-------------------------|--|
| Version                 | M12 screw  |
| Conductor cross-section | 35.00 ... 240.00 mm <sup>2</sup><br>(AWG 2 ... AWG -3) |

#### DC link (for braking resistor)

|               |           |
|---------------|-----------|
| PE connection | M12 screw |
|---------------|-----------|

#### Max. motor cable length


|          |                   |
|----------|-------------------|
| Shielded | 150 m (492.13 ft) |
|----------|-------------------|



Figure similar

### Converter losses to EN 50598-2\*

|  |          |
|--|----------|
| Efficiency class                                     | IE2      |
| Comparison with the reference converter (90% / 100%) | -34.60 % |



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

### Standards

**Compliance with standards** UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH

**CE marking** EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC

### Operator panel: Intelligent Operator Panel (IOP-2)

#### Screen

|                   |                 |
|-------------------|-----------------|
| Display design    | LCD colors      |
| Screen resolution | 320 x 240 Pixel |

#### Mechanical data

|                      |                     |
|----------------------|---------------------|
| Degree of protection | IP55 / UL type 12   |
| Net weight           | 0.13 kg (0.30 lb)   |
| Width                | 70.0 mm (2.76 in)   |
| Height               | 106.85 mm (4.21 in) |
| Depth                | 19.65 mm (0.77 in)  |

#### Ambient conditions

##### Ambient temperature during

|           |                                   |
|-----------|-----------------------------------|
| Operation | 0 ... 50 °C (32 ... 122 °F)       |
|           | 55 °C only with door mounting kit |
| Storage   | -40 ... 70 °C (-40 ... 158 °F)    |
| Transport | -40 ... 70 °C (-40 ... 158 °F)    |

##### Relative humidity at 25°C during

|                |      |
|----------------|------|
| Max. operation | 95 % |
|----------------|------|

### Approvals

**Certificate of suitability** CE, cULus, EAC, KCC, RCM