

Article No. : 6SL3210-1PE18-0AL1



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

Input

Number of phases	3 AC
Line voltage	380 ... 480 V ±10 %
Line frequency	47 ... 63 Hz
Rated current (LO)	10.10 A
Rated current (HO)	8.80 A

Output

Number of phases	3 AC
Rated voltage	400V IEC 480V NEC ¹⁾
Rated power (LO)	3.00 kW 4.00 hp
Rated power (HO)	2.20 kW 3.00 hp
Rated current (LO)	7.70 A
Rated current (HO)	5.90 A
Max. output current	11.80 A
Pulse frequency	4 kHz
Output frequency for vector control	0 ... 200 Hz
Output frequency for V/f control	0 ... 550 Hz

Overload capability

Low Overload (LO)

1.1 x rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s
1.5 x rated output current (i.e. 150 % overload) for 3 s with a cycle time of 300 s

High Overload (HO)

1.5 x output current rating (i.e., 150 % overload) for 57 s with a cycle time of 300 s
2 x output current rating (i.e., 200 % overload) for 3 s with a cycle time of 300 s

General tech. specifications

Power factor λ	0.85
Offset factor $\cos \varphi$	0.95
Efficiency η	0.96
Sound pressure level (1m)	72 dB
Power loss	0.12 kW
Filter class (integrated)	Class A

Ambient conditions

Cooling	Internal air cooling
Cooling air requirement	0.005 m ³ /s (0.177 ft ³ /s)
Installation altitude	1,000 m (3,280.84 ft)

Ambient temperature

Operation LO	-10 ... 40 °C (14 ... 104 °F)
Operation HO	-10 ... 50 °C (14 ... 122 °F)
Transport	-25 ... 55 °C (-13 ... 131 °F)
Storage	-25 ... 55 °C (-13 ... 131 °F)

Relative humidity

Max. operation	95 % RH, condensation not permitted
----------------	-------------------------------------

Connections

Line side

Version	Plug-in screw terminals
Conductor cross-section	1.50 ... 2.50 mm ² (AWG 16 ... AWG 14)

Motor end

Version	Plug-in screw terminals
Conductor cross-section	1.50 ... 2.50 mm ² (AWG 16 ... AWG 14)

Max. motor cable length

Shielded	50 m (164.04 ft)
Unshielded	100 m (328.08 ft)

Mechanical data

Degree of protection	IP20 / UL open type
Frame size	FSA
Net weight	1.50 kg (3.31 lb)

Dimensions

Width	73 mm (2.87 in)
Height	196 mm (7.72 in)
Depth	165 mm (6.50 in)

Standards


Compliance with standards	UL, cUL, CE, C-Tick (RCM), SEMI F47
CE marking	Low-voltage directive 2006/95/EC

Data sheet for SINAMICS Power module PM240-2

Article No. : 6SL3210-1PE18-0AL1

Converter losses to IEC61800-9-2*

Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	31.40 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*calculated values

¹⁾The output current and HP ratings are valid for the voltage range 440V-480V